

Features

- Watertight seal around lid
- Automatic pressure release valve
- Stackable interlocking system
- Thick body material
- Nylon pins, corrosion free
- Body: polypropylene copolymer

RS PRO Waterproof Case, Polypropylene, Black



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Watertight Case, w/ Cubed Foam

For ultimate safe and secure transport, the RS PRO roller waterproof travel case provides you with superior protection from the elements, water, dust and impact when transporting fragile and valuable objects. It is the ideal professional solution. The benefits of the RS PRO equipment case are endless from being completely watertight (IP67) to dealing with extreme temperatures from -51°C to +90°C.

Pre-Cubed foam inserts safely protect any components, sensitive equipment, and documents within the indestructible military grade equipment case.

General Specifications

Material	Polypropylene
Internal Length	See details below
Internal Width	See details below
Internal Height	See details below
Internal Dimensions	See details below
External Dimensions	See details below
Pack Q'ty	See details below
Foam	See details below
Watertight or Waterproof	Yes
Wheels	No
Material Type	Plastic
Colour	See details below
IP Rating	IP67
Weight	See details below

Stock No.	Product Name	Internal Dimensions (L x W x H mm)	External Dimension (L x W x H mm)	Pack Q'ty	Colour	Foam	Weight (Kg)
707761	Waterproof Case	157 x 82 x 41	175 x 115 x 47	12	Black	No	0.14
707762	Waterproof Case	157 x 82 x 41	175 x 115 x 47	1	Black	No	0.14
707763	Waterproof Case	157 x 82 x 41	175 x 115 x 47	12	Black	Yes	0.15
707764	Waterproof Case	157 x 82 x 41	175 x 115 x 47	1	Black	Yes	0.15
707765	Waterproof Case	212 x 140x 47	230 x 175 x 53	12	Black	Yes	0.29
707766	Waterproof Case	212 x 140x 47	230 x 175 x 53	1	Black	Yes	0.29
707768	Waterproof Case	316 x 195 x 53	350 x 230 x 59	6	Black	Yes	0.56
707769	Waterproof Case	316 x 195 x 53	350 x 230 x 59	1	Black	Yes	0.56
707770	Waterproof Case	316 x 195 x 81	350 x 230 x 86	4	Black	Yes	0.66
707771	Waterproof Case	316 x 195 x 81	350 x 230 x 86	1	Black	Yes	0.66
707784	Waterproof Case	212 x 140 x 47	230 x 175 x 53	12	Black	Yes	3.12
707785	Waterproof Case	212 x 140 x 47	230 x 175 x 53	1	Black	Yes	0.26

Approvals

Declarations	REACH DoC
--------------	-----------

Similar Products

Stock No.	Brand	Product Name	Internal Dimensions (L x W x H mm)	External Dimension (L x W x H mm)	Pack Q'ty	Colour	IP Rating
707812	RS PRO	Assortment Box, 6 compartments	155 x 98 x 31H	166 x 105 x 31H	120	Transparent	N/A
707813	RS PRO	Assortment Box, 6 compartments	155 x 98 x 31H	166 x 105 x 31H	5	Transparent	N/A
707819	RS PRO	Assortment Box, 15 compartments	155 x 98 x 31H	166 x 105 x 31H	120	Transparent	N/A
707820	RS PRO	Assortment Box, 15 compartments	155 x 98 x 31H	166 x 105 x 31H	5	Transparent	N/A
707816	RS PRO	Assortment Box, 13 compartments	155 x 98 x 31H	166 x 105 x 31H	120	Transparent	N/A
707817	RS PRO	Assortment Box, 13 compartments	155 x 98 x 31H	166 x 105 x 31H	5	Transparent	N/A
707814	RS PRO	Assortment Box, 10 compartments	155 x 98 x 31H	166 x 105 x 31H	120	Transparent	N/A
707815	RS PRO	Assortment Box, 10 compartments	155 x 98 x 31H	166 x 105 x 31H	5	Transparent	N/A
707839	RS PRO	Packaging Case	248 x 160 x 39	260 x 210 x 44	42	Black	N/A
707840	RS PRO	Packaging Case	248 x 160 x 39	260 x 210 x 44	1	Black	N/A
707843	RS PRO	Packaging Case	272 x 190 x 73	280 x 240 x 76	46	Black	N/A
707844	RS PRO	Packaging Case	272 x 190 x 73	280 x 240 x 76	1	Black	N/A
707831	RS PRO	Transit Case	324 x 252 x 87	340 x 298 x 96	10	Black	N/A
707832	RS PRO	Transit Case	324 x 252 x 87	340 x 298 x 96	1	Black	N/A
707841	RS PRO	Packaging Case	363 x 244 x 115	370 x 307 x 121	8	Black	N/A
707842	RS PRO	Packaging Case	363 x 244 x 115	370 x 307 x 121	1	Black	N/A
707837	RS PRO	Packaging Case	385 x 235 x 98	395 x 300 x 103	10	Black	N/A
707838	RS PRO	Packaging Case	385 x 235 x 98	395 x 300 x 103	1	Black	N/A
707821	RS PRO	Assortment Box	315 x 240 x 46	325 x 255 x 56	18	Transparent	N/A
707822	RS PRO	Assortment Box	315 x 240 x 46	325 x 255 x 56	1	Transparent	N/A
707833	RS PRO	Tool Case	N/A	420 x 303 x 400	2	Blue/White	N/A
707834	RS PRO	Tool Case	N/A	420 x 303 x 400	1	Blue/White	N/A
707835	RS PRO	Tool Case	N/A	420 x 303 x 400	2	Blue/White	N/A
707836	RS PRO	Tool Case	N/A	420 x 303 x 400	1	Blue/White	N/A

707826	RS PRO	Packaging Case	415 x 280 x 190	465 x 355 x 210	3	Black	IP65
707827	RS PRO	Packaging Case	415 x 280 x 190	465 x 355 x 210	1	Black	IP65
707823	RS PRO	Packaging Case	415 x 280 x 125	465 x 355 x 145	4	Black	IP65
Stock No.	Brand	Product Name	Internal Dimensions (L x W x H mm)	External Dimension (L x W x H mm)	Pack Q'ty	Colour	IP Rating
707825	RS PRO	Packaging Case	415 x 280 x 125	465 x 355 x 145	1	Black	IP65
707828	RS PRO	Packaging Case	520 x 350 x 125	572 x 425 x 144	3	Black	IP65
707829	RS PRO	Packaging Case	520 x 350 x 125	572 x 425 x 144	1	Black	IP65
707763	RS PRO	Waterproof Case	157 x 82 x 41	175 x 115 x 47	12	Black	IP67
707764	RS PRO	Waterproof Case	157 x 82 x 41	175 x 115 x 47	1	Black	IP67
707806	RS PRO	Assortment Box	157 x 82 x 41	175 x 115 x 47	12	Transparent	IP67
707807	RS PRO	Assortment Box	157 x 82 x 41	175 x 115 x 47	1	Transparent	IP67
707761	RS PRO	Waterproof Case	157 x 82 x 41	175 x 115 x 47	12	Black	IP67
707762	RS PRO	Waterproof Case	157 x 82 x 41	175 x 115 x 47	1	Black	IP67
707765	RS PRO	Waterproof Case	212 x 140x 47	230 x 175 x 53	12	Black	IP67
707766	RS PRO	Waterproof Case	212 x 140x 47	230 x 175 x 53	1	Black	IP67
707808	RS PRO	Assortment Box	212 x 140 x 47	230 x 175 x 53	12	Transparent	IP67
707809	RS PRO	Assortment Box	212 x 140 x 47	230 x 175 x 53	1	Transparent	IP67
707784	RS PRO	Watertight Case	212 x 140 x 47	230 x 175 x 53	12	Black	IP67
707785	RS PRO	Watertight Case	212 x 140 x 47	230 x 175 x 53	1	Black	IP67
707768	RS PRO	Waterproof Case	316 x 195 x 53	350 x 230 x 59	6	Black	IP67
707769	RS PRO	Waterproof Case	316 x 195 x 53	350 x 230 x 59	1	Black	IP67
707810	RS PRO	Assortment Box	316 x 230 x 53	350x 230 x 59	6	Transparent	IP67
707811	RS PRO	Assortment Box	316 x 230 x 53	350x 230 x 59	1	Transparent	IP67
707770	RS PRO	Waterproof Case	316 x 195 x 81	350 x 230 x 86	4	Black	IP67
707771	RS PRO	Waterproof Case	316 x 195 x 81	350 x 230 x 86	1	Black	IP67
707755	RS PRO	Waterproof Case	235 x 180 x 105	258 x 243 x 117.5	4	Black	IP67
707756	RS PRO	Waterproof Case	235 x 180 x 105	258 x 243 x 117.5	1	Black	IP67
707786	RS PRO	Watertight Case	258 x 243 x 118	366 x 464 x 176	4	Orange	IP67
707787	RS PRO	Watertight Case	258 x 243 x 118	366 x 464 x 176	1	Orange	IP67
707757	RS PRO	Waterproof Case	235 x 180 x 156	258 x 243 x 167.5	4	Black	IP67
707758	RS PRO	Waterproof Case	235 x 180 x 156	258 x 243 x 167.5	1	Black	IP67
707788	RS PRO	Watertight Case	258 x 243 x 168	366 x 464 x 176	4	Orange	IP67
707790	RS PRO	Watertight Case	258 x 243 x 168	366 x 464 x 176	1	Orange	IP67
707791	RS PRO	Watertight Case	336 x 300 x 148	366 x 464 x 176	4	Orange	IP67
707792	RS PRO	Watertight Case	336 x 300 x 148	366 x 464 x 176	1	Orange	IP67
707793	RS PRO	Watertight Case	336 x 300 x 148	366 x 464 x 176	4	Brown	IP67
707794	RS PRO	Watertight Case	336 x 300 x 148	366 x 464 x 176	1	Brown	IP67
707772	RS PRO	Watertight Case	380 x 270 x 115	414 x 345 x 129	2	Black	IP67
707774	RS PRO	Watertight Case	380 x 270 x 115	414 x 345 x 129	1	Black	IP67
707776	RS PRO	Watertight Case	380 x 270 x 160	414 x 345 x 174	2	Black	IP67
707777	RS PRO	Watertight Case	380 x 270 x 160	414 x 345 x 174	1	Black	IP67
707778	RS PRO	Watertight Case	400 x 230 x 260	456 x 290 x 318	2	Black	IP67
707779	RS PRO	Watertight Case	400 x 230 x 260	456 x 290 x 318	1	Black	IP67
707798	RS PRO	Watertight Case	426 x 290 x 159	464 x 366 x 176	2	Green	IP67
707799	RS PRO	Watertight Case	426 x 290 x 159	464 x 366 x 176	1	Green	IP67
707759	RS PRO	Waterproof Case	426 x 290 x 159	464 X 366 X 176	2	Black	IP67
707760	RS PRO	Waterproof Case	426 x 290 x 159	464 X 366 X 176	1	Black	IP67

707796	RS PRO	Watertight Case	426 x 290 x 159	464 x 366 x 176	2	Orange	IP67
707797	RS PRO	Watertight Case	426 x 290 x 159	464 x 366 x 176	1	Orange	IP67
707775	RS PRO	Watertight Case	465 x 335 x 125	502x 415 x 141	1	Black	IP67
Stock No.	Brand	Product Name	Internal Dimensions (L x W x H mm)	External Dimension (L x W x H mm)	Pack Q'ty	Colour	IP Rating
707780	RS PRO	Watertight Case	465 x 335 x 220	502 x 415 x 246	1	Black	IP67
707781	RS PRO	Watertight Case	500 x 350 x 280	555 x 428 x 306	1	Black	IP67
707803	RS PRO	Roller Watertight Case	500 x 350 x 280	555 x 428 x 326	1	Black	IP67
707800	RS PRO	Watertight Case	500 x 350 x 211	555 x 428 x 211	1	Orange	IP67
707801	RS PRO	Roller Watertight Case	538 x 405 x 245	604 x 473 x 283	1	Black	IP67
707804	RS PRO	Roller Watertight Case	620 x 460 x 250	687 x 528 x 276	1	Black	IP67
707805	RS PRO	Roller Watertight Case	620 x 460 x 340	687 x 528 x 376	1	Black	IP67
707783	RS PRO	Watertight Case	750 x 480 x 400	816 x 540 x 426	1	Black	IP67
707782	RS PRO	Watertight Case	800 x 370 x 140	850 x 440 x 158	1	Black	IP67

Stock No. 707-761 (Q'ty: 12pcs)

Stock No. 707-762 (Q'ty: 1pc)

IP67



- External dimension 175 x 115 x 47H mm
- Internal dimension 157 x 82 x 41H mm
- Weight: 0.14kg
- Temperature rating: -10 to 80°C
- Capacity: Capacity: 0.527 lt
- Watertight seal around lid
- Automatic pressure release valve
- Stackable interlocking system
- Thick body material

Stock No. 707-784 (Q'ty: 12pcs)
Stock No. 707-785 (Q'ty: 1pc)

IP67



- External dimension 230 x 175 x 53H mm
- Internal dimension 212 x 140 x 47H mm
- Weight: 0.26kg
- Temperature rating: -10 to 80°C
- Capacity: Capacity: 1.39 lt
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins corrosion free
- Foam

Stock No. 707-763 (Q'ty: 12pcs)

Stock No. 707-764 (Q'ty: 1pc)

IP67



- External dimension 175 x 115 x 47H mm
- Internal dimension 157 x 82 x 41H mm
- Weight: 0.15kg
- Temperature rating: -10 to 80°C
- Capacity: Capacity: 0.527 lt
- Watertight seal around lid
- Automatic pressure release valve
- Stackable interlocking system
- Thick body material
- Pre-Cut cubed foam

Stock No. 707-765 (Q'ty: 12pcs)

Stock No. 707-766 (Q'ty: 1pc)

IP67



- External dimension 230 x 175 x 53H mm
- Internal dimension 212 x 140 x 47H mm
- Weight: 0.29kg
- Temperature rating: -10 to 80°C
- Capacity: Capacity: 1.39 lt
- Watertight seal around lid
- Automatic pressure release valve
- Stackable interlocking system
- Thick body material
- Pre-Cut cubed foam

Stock No. 707-768 (Q'ty: 6pcs)

Stock No. 707-769 (Q'ty: 1pc)

IP67



- External dimension 350 x 230 x 59H mm
- Internal dimension 316 x 195 x 53H mm
- Weight: 0.56kg
- Temperature rating: -10 to 80°C
- Capacity: Capacity: 3.26 lt



- Watertight seal around lid
- Automatic pressure release valve
- Stackable interlocking system
- Thick body material
- Pre-Cut cubed foam

Stock No. 707-770 (Q'ty: 4pcs)

Stock No. 707-771 (Q'ty: 1pc)

IP67



- External dimension 350 x 230 x 86H mm
- Internal dimension 316 x 195 x 81H mm
- Weight: 0.66kg
- Temperature rating: -10 to 80°C
- Capacity: Capacity: 4.99 lt



- Watertight seal around lid
- Automatic pressure release valve
- Stackable interlocking system
- Thick body material
- Pre-Cut cubed foam