

COMPOSITION OF 435 TOOLS IN FOAM MODULES FOR TROLLEYS

CP-435MM

SAM Outillage



10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:34





DESCRIPTION

COMPOSITION OF 435 TOOLS IN FOAM MODULES FOR TROLLEYS

Composition of 435 foam module tools for 41 series tool chest or others.

SPECIFIC DATA

Designation	435 TOOLS IN FOAM MODULE
Sales reference	CP-435MM
Weight (kg)	42.81
Guarantee	O SAM TOOL guarantee.

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:34



Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

Toolset



x 1

Selection of tightening tools - foam module 3/3
CP-138PM



x 1

Screw driving bits ph + hex

E-900J10

Ref : E-900J10



x 1

Screw driving bits pz +tx

E-910J10

Ref : E-910J10



x 1

Screw driving bits fte +txr

E-920J10

Ref : E-920J10



x 1

3/8" sliding handle

J-120

Ref : J-120



x 1

1/2" site ratchet with lever reversion

J-157B

Ref : J-157B



x 2

Straight 3/8" extensions

J-2...

Ref : J-208 - J-210



x 1

3/8" joint

J-240

Ref : J-240



x 17

3/8" short hexagonal sockets in mm

JH-...

Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22



x 2

LONG SOCKET 6-FLAT 3/8" 28 MM

JHL-...

Ref : 16 - 21



x 5

3/8" sockets for Torx® head

JTX-...

Ref : 10 - 11 - 12 - 14 - 16

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å.

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:34



	x 15	1/4" short hexagonal key socket (mm) R-...Douilles_1/4_MM Ref : 3,5 - 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15
	x 1	1/4" sliding handle R-120 Ref : R-120
	x 1	Site 1/4" ratchet R-157B Ref : R-157B
	x 2	Straight 1/4" extensions R-21... Ref : R-210 - R-211
	x 1	Flexible 1/4" extension R-220 Ref : R-220
	x 1	Fitted 1/4" extension R-225 Ref : R-225
	x 1	1/4" joint R-240 Ref : R-240
	x 1	1/4" bit holder socket RD-1 Ref : RD-1
	x 6	1/4" single-piece screwdriver sockets for hollow hexagonal screws RS-... Ref : 3 - 4 - 5 - 6 - 7 - 8
	x 1	Sets of 6 screwdriver sockets 1/4" for 6-flat socket head screws on storage rack RS-J6R Ref : RS-J6R
	x 1	Set of 8 screwdriver sockets 1/4" for Torx® imprint on storage rack RT-J8R Ref : RT-J8R
	x 5	1/4" sockets for Torx® head RTX-... Ref : 4 - 5 - 6 - 7 - 8
	x 1	1/2" sliding locking handle S-120 Ref : S-120
	x 1	1/2" site ratchet with lever reversion S-157B Ref : S-157B



x 1



x 1

Straight 1/2" extensions

S-2...

Ref : S-215



x 1

1/2" joint

S-240

Ref : S-240



x 18

1/2" short hexagonal sockets in mm

SH-...

Ref : 10 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 - 27 - 30 - 32



x 5

1/2" long bi-hexagonal sockets in mm

SL-...Douilles_MM

Ref : 14 - 15 - 17 - 19 - 22



x 3

1/2" sockets for Torx® head

STX-...

Ref : 18 - 20 - 24

3/3 FOAM MODULE 12 PLIERS

CP-12MM



x 1

Polished chrome-plated universal pliers with spring

204-R...G

Ref : 204-R18G



x 1

Mechanic's diagonal chrome-plated cutting pliers with spring

232-R...G

Ref : 232-R18G



x 1

Straight half-round nose pliers, polished chrome-plate

237-...G

Ref : 237-20G



x 1

Polished chrome-plated angled half-round nose pliers with spring

239-R20G



x 1

Mat chrome-plated straight nose outer circlips pliers

195-...A

Ref : 195-17A



x 1

Mat chrome-plated 90° elbowed nose outer circlips pliers

196-...A

Ref : 196-17A



x 1

Burnished finish straight nose inner circlips pliers

190-...A

Ref : 190-17A



x 1

Mat chrome-plated 90° elbowed nose inner circlips pliers

191-...A

Ref : 191-17A



x 1

 x 1 High-capacity lock grip pliers
212-25

 x 1 Crimping pliers
241-42

 x 1 Polished chrome-plated stacked-branch multigrip pliers
209-25B

 x 1 Mechanic's end nippers
229-...
Ref : 229-25

MODM 3/3 88 SCREWDRIVER+WRENCHES MA.
CP-88MM

 x 1 Flexible screwdriver 6 mm
23-...
Ref : 7 mm

 x 1 Ratchet telescopic screwdriver with magnetic bit holder
T-PE

 x 9 Rack of 9 male 6-flat keys with spherical head in mm
67-AR9A
Ref : 1,5 - 2 - 2,5 - 3 - 4 - 5 - 6 - 8 - 10 mm

 x 9 Rack of 9 Torx® male keys
66-R9A
Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40

 x 9 Torx® S1 round blade screwdriver
T-...X
Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40

 x 2 Testing screwdriver
268-...
Ref : 6-24V et 100-500V

 x 3 SCREWDRIVER ELECTRICIAN INSULATED 1000V
ZTC-...E
Ref : N°2 - N°3 - N°4

 x 2 SCREWDRIVER PHILLIPS® INSULATED 1000V
ZTC-...P
Ref : N°1 - N°2

 x 1 Electrician's S1 round blade slotted head screwdriver
T-...E
Ref : 4x100 mm

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:51:34





x 1

	x 3	Mechanic's S1 round blade slotted head screwdriver T-...M Ref : 5,5x100 - 6,5x100 - 8x150 mm
	x 3	Phillips® S1 round blade screwdriver T-...P Ref : N°1 - N°2 - N°3
	x 1	Phillips® S1 round blade tom thumb screwdriver T-...P_Tom_pouce Ref : N°2
	x 1	Electrician's S1 round blade tom thumb slotted head screwdriver T-...E_Tom_pouce Ref : 6,5x35 mm
	x 30	31-piece screwdriver bit set E900-J30B

3/3 FOAM MOD 24 STRIK TOOLS
CP-24MM

	x 1	SAMSOPLUS® riveting hammer, three-material handle 310-...TM Ref : 32 mm
	x 1	Mallets with interchangeable tips 320-...D Ref : 32 mm
	x 1	Short tape measures with two-material casings UB-...N Ref : 2 m
	x 1	Slide callipers with 1/2"0 mm precision 710-P-8
	x 1	Plastic body scriber 665-11
	x 6	Short drift punches 7-C...A Ref : 1,9 - 2,9 - 3,9 - 4,9 - 5,9 - 7,9 mm
	x 1	Knife with retractable blade 378-7
	x 5	Set of 5 helix pullers 761-C-5



x 1



x 1

Fitted flat hand file

LPM-...E

Ref : 250 mm



x 1

Fitted round files

LR-...-E

Ref : 250 mm



x 1

Fitted half-round files

LDR-...-E

Ref : 250 mm



x 2

Constant section chisels with comfortable handle

3-...-G

Ref : 175 - 200 mm



x 1

Punch 10 mm

8N-...A

Ref : 8 mm

3/3 FOAM MOD 40 WRENCHES

CP-40MM



x 19

Extra-thin combination wrench

50N-...

Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 mm



x 9

Set of 9 multi-nut inch / metric ratchet combination spanners

50-HCJ9

Ref : 10 - 11 - 12 - 13 - 14 - 16 - 17 - 18 - 19 mm



x 8

Set of 8 offset ring wrenches in mm

105-J8D



x 4

Torx® polygonal straight wrench

9T-...

Ref : E6xE8 - E10xE12 - E14xE18 - E20xE24 mm



x 1

MODM 3/3 78 SOCKET+SCREWDRIVER

CP-78MM



x 10

Set of sockets for rounded nuts and pins

74NJ-J10

Ref : 6 - 8 - 10 - 11 - 12 - 13 - 14 - 15 - 17 - 19 - 21 - 24 - 27 mm



x 9

1/2" short hexagonal sockets in mm

SH-...

Ref : 10 - 11 - 12 - 14 - 16 - 18 - 20 - 22 - 24 mm



x 5

Socket sets 1/2" long impact car wheel nuts

19141-95

Ref : 15 - 17 - 19 - 21 - 22 mm



x 1

 x 10
1/2" long hexagonal impact sockets in mm
NS-...L
Ref : 10 - 12 - 13 - 14 - 15 - 19 - 21 - 22 - 30 - 32 mm

 x 1
Shock socket extra-long slim 1/2" "
19141-...M
Ref : 36 mm

 x 7
1/2" screwdriver socket - hexagonal
SC-...1/2_6_pans
Ref : H5 - H6 - H7 - H8 - H10 - H12 - H14

 x 8
1/2" Torx® screwdriver socket
ST-...-...
Ref : T25 - T27 - T30 - T40 - T45 - T50 - T55 - T70

 x 10
1/2" XZN® screwdriver socket
SD-...-...
Ref : L55 - M6 - M8 - M10 - M12 - M14L100 : M6 - M8 - M10 - M12 - M14

 x 8
1/2" ribes screwdriver socket
SR-...
Ref : L100 : RB5 - RB6 - RB7 - RB8 - RB10 - RB12L200 : RB8 - RB9

MODM 3/3 55 OUT REV AUTOMOBILE
CP-55MM

 x 1
Pneumatic disc brake piston pushing tool
FD1-PN

 x 1
Quick tips for fitting
1906.../1907...
Ref : 19062

 x 1
Universal 2 pins brake piston pusher flange adapter
P3110-25

 x 1
Universal 3 pins brake piston pusher flange adapter
P3110-26

 x 3
Set of hexagonal flare nut ring wrenches in mm
104-H-...
Ref : 10x11 - 11x13 - 12x14

 x 3
5 sides socket 1/2" 10 mm
3122-...
Ref : 10 - 14 - 19 mm

 x 1
Caliper for brake disc
3510B

	x 1	8 brake lining thickness gauge FD-J8
	x 1	Wire brush 2880
	x 1	Down brake pad cleaning file 2760
	x 7	Petrol spark plug 3/8" socket with joint BDC-...-JC Ref : 8 - 9 - 10 - 12 - 14 - 16 - 21 mm
	x 4	Set of 4 clamps for flexible pipes FT-4
	x 1	Two angles self locking pliers 208-35
	x 17	3/8" engine drain socket set 628-SET
	x 1	Torx® socket t55, square drive 3/8" 3953-T55
	x 1	1/2" breakthrough XZN® drain socket SDP-18
	x 1	3-finger car oil filter wrench 628-3
	x 1	Universel pliers slotted for oil filter 3930
	x 6	Cap sockets 3/8" for oil filters 628-...Douilles_coiffes Ref : 24 - 27 - 30 - 32 - 36 - 38 mm
	x 1	Bell oil filter socket 106/15 3955-...-... Ref : 3955-76-14