



**MADE IN
GERMANY**

3 YEARS
MANUFACTURER
GUARANTEE



Product number

1319250

EAN

4007123680153

DESCRIPTION

- Heavy Duty reel, mounted to an extremely sturdy, powder-coated steel-tube frame. Reel body made from highly break-resistant, special rubber.
- With hinged rotary handle for comfortable rolling up.
- CEE-plug 400 V/32 A 5-pole,
 - 1 CEE-socket 400 V/32 A 5-pole,
 - 1 CEE-socket 400 V/16 A 5-pole,
- 3 water-jet protected sockets 230 V.
- With 4-pin safety cut-out and thermal overload protection.
- RCD circuit breaker 30 mA,
 - automatic fuse 400 V/16 A 3-pole,
 - automatic fuse 230 V/16 A.

TECHNICAL DATA

Cable quality	Rubber-Neoprene	Plug system CEE socket	CEE 1x 16 A 3P+N+E (5p) 400 V/CEE 1x 32 A 3P+N+E (5p) 400 V
Cable length	25 m	Plug system socket	Type F (Protective contact)
Cable designation	H07RN-F 5G4,0	Plug system plug	CEE 32 A 3P+N+E (5p) 400 V
Cable colour	black	Nominal input voltage	230 V/400 V
Reel diameter	380 mm	Degree of protection (IP)	IP44

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	16.7 kg
Weight of product (without packaging)	16.7 kg	Dimension LxWxH (incl. packing)	28 cm x 38 cm x 51 cm
Dimension LxWxH (without packing)	28 cm x 38 cm x 51 cm		

SCOPE OF DELIVERY

Professional Brobusta CEE 2 FI IP44 cable reel