



M18 HOAL-O

M18™ HIGH OUTPUT AREA LIGHT

4000 lumens TRUEVIEW™ of High Definition Output

Up to 12 hours of run time on M18™ REDLITHIUM™ 5.0 Ah battery pack

120° rotatable light head and integrated key holes for horizontal and vertical hanging

Impact resistant design and durable roll cage to protect the light from rough jobsite conditions

AC/DC versatility: Powered by MILWAUKEE® M18™ batteries, or mains plug supply


Easy one-handed transport with built-in carry handles

Low battery indicator, light flashes when battery pack is low on charge

Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Max. light output High/Medium/Low/Strobe (lumens)	4000/ 2000/ 1200
Max. run time with M18 B5 battery [h]	3/ 6/ 12
Weight with battery pack (EPTA) (kg)	3.3 (M18 B5)
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933478118