



M18 MDTL-O

M18™ MULTI-DIRECTIONAL TASK LIGHT

- TRUEVIEW™ high definition lighting with up to 4,500 lumens
- 3 individual light heads for task or area lighting
- 9 total output modes to manage output or run time
- Magnetic base, integrated hook, and screw holes for optimal surface mounting
- 270° horizontal rotation and 270° vertical articulation
- Integrated handles for easy carrying
- Highly durable and impact resistant design to withstand drops up to 2 m
- AC/DC versatility: Powered by MILWAUKEE® M18™ batteries, or mains plug supply
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Max. light output Area Mode	4,500/ 2,000/ 1,200
High/Medium/Low [lumens]	
Max. run time on area mode	3/ 6/ 11
with M18 B5 battery [h]	
Weight with battery pack (EPTA)	3.75 (M18 B5)
(kg)	
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article number	4933498149