

M18 FN16GA-O

M18 FUEL™ 16 GA ANGLED NAIL FINISH NAILER 2-MODE

Fire 16 Gauge nails with a 20° pitch

Tool-free, quick and easy depth adjustment to assure nails are driven sub-flush

No gas cartridges and no cleaning required, designed to deliver durability and reliability to the most demanding users with very little maintenance

Excellent power to consistently seat nails sub-flush to the surface in hardwoods

Different shaped noses stored on board allows the user to get the best finish no matter what the application

Small work contact bracket allows the user to fire and sink nails at a more acute angle

Ready to Fire Nail Technology eliminates ramp-up time between each nail discharge

Dry-Fire lockout stops the tool being fired when there are no nails left in the magazine

Fires up to 1200 nails per charge on a REDLITHIUM™ 2.0 Ah battery pack for maximum productivity

Quick access and easy clearing of jams


LED work light illuminates the work surface for better placement of nails

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Collation angle [degrees]	20
Nail diameter [mm]	1.6
Nail type (mm)	32 - 64
Magazine capacity nails	110
Weight with battery pack (EPTA) (kg)	3.3 (M18 B2)
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article number	4933499154