

DSC-P5



With the Cyber-shot® DSC-P5 digital camera, you're not just getting a sleek little camera in an expertly-designed compact case - you're getting a 3.2 Effective (3.3 Gross) MP CCD, 3X optical/6X precision digital zoom, and a host of easy-to-use features that give you the power to take pictures like a pro. Weighing in at less than 8 ounces and measuring just a hair over 4"x2"x1", you can keep the DSC-P5 in your pocket and never miss the opportunity to capture a moment you never want to forget!

features

features

- ▶ Saves to Memory Stick® Media of any storage capacity
- ▶ 1/1.8" 3.2 Effective MP Super HAD™ CCD, 3.3 Gross MP
- ▶ QXGA (2048x1536), 3:2 QXGA (2048x1360), UXGA (1600x1200), SXGA (1280x960), VGA (640x480) Sizes
- ▶ 3X Optical Zoom Lens / 6X Precision Digital Zoom
- ▶ High-speed scan auto-focus with AF Illuminator light, 5 manual focus presets
- ▶ Selectable JPEG, TIFF, voice memo, e-mail, and text still image modes
- ▶ Intelligent Flash w/Adjustable Level & selectable Red Eye Reduction
- ▶ Manual focus with 5-step presets
- ▶ Twilight Scene Mode Program Auto-exposure, 4 mode auto white exposure
- ▶ Eye-level true-zoom Optical Viewfinder, 1.5" 123K Pixel LCD Viewfinder with AccuPower™ Meter
- ▶ JPEG (Fine/Standard)
- ▶ Two-shot burst mode
- ▶ MPEG-EX (EXtended) 160x112 and 320x240 Audio/Video modes with 6X cue/review and divide/delete editing
- ▶ MPEG-HQ (High Quality) 320x240 Audio/Video mode with 16fps full screen playback & hi-sampling rate audio
- ▶ Clip Motion 160x120 and 80x72 Animated GIF Modes

DSC-P5



☐ specs

specifications

Imager:	1/1.8" 3.2 Effective (3.3 Gross) MP CCD
Lens/Optical Z, Aperture:	Sony, 3X f2.8~5.6
Focal Length:	8~24mm
35MM Equivalency:	39~117mm
Digital Zoom:	Precision, 2X
Auto Focus:	Contrast Detect
Manual Focus:	Yes, 5 Step
White Balance:	Auto/InD/OutD/1Push
Shutter Priority (range):	N/A (Auto)
Manual Exposure:	N/A
Program AE:	Twilight
Flash Modes:	Auto/Forced/Off
LCD:	1.5" 123K Pixel
Recording Media:	Memory Stick
Still Image Formats:	JPEG/GIF/TIFF
4.1MP Image:	N/A
QXGA Image:	2048 x 1536
UXGA Image:	1600 x 1200
SXGA Image:	1280 x 960
XGA Image:	N/A
VGA Image:	640 x 480
Burst Mode:	2Frames, 2fps
E-mail Mode:	Yes, adds 320x240
Voice Memo Mode:	Yes
Picture Effects:	4 Modes
Movie Modes:	MPEG / MPEG HQ
Clip Motion Animated GIF:	160x120, 80x72

Storage Supplied:	8MB Memory Stick
Connections:	Video/USB/AC Pwr
Battery Requirement:	InfoLithium C
Date/Time Stamp:	Yes
Slideshow Mode:	Yes
Battery Indicator:	Yes
Self Timer:	Yes
Microphone/Speaker:	Yes
Battery Supplied:	NP-FC10
USB OS Compatibility	Windows® 98/98SE/ME/2000 Professional Macintosh® OS 8.5.1/8.6/9.0/9.1

- ▶ Playback Zoom with selectable resolution
- ▶ Trimming function
- ▶ In-camera re-size function
- ▶ A/V output
- ▶ USB Connector with cable & driver for Windows® 98/98SE/Me/2000 Professional, Macintosh® OS 8.5.1/8.6/9.0/9.1
- ▶ Supplied Acc: rechargeable InfoLithium® C battery, AC-LS1 AC adapter/in-camera charger, A/V output cable, USB cable, wrist strap, 8 MB Memory Stick® Digital Media

DSC-P5



☐ accessories

accessories

Model #:	Description:		
Memory Sticks:			
MSA128A	128 MB Memory Stick® Media	Info	add to cart
MSA64A	64 MB Memory Stick® Media	Info	add to cart
MSA16A	16 MB Memory Stick® Media	Info	add to cart
MSA32A	32 MB Memory Stick® Media	Info	add to cart
MSA8A	8 MB Memory Stick® Media	Info	add to cart
Memory Stick Adapters:			
MSACFD2MA	Memory Stick® Floppy Disk Adaptor	Info	add to cart
MSACUS1A	Memory Stick® Reader/Writer for USB	Info	add to cart
MSACUS5	Memory Stick® Reader/Writer Optical Mouse	Info	add to cart
MSACA8	Memory Stick® Case	Info	add to cart
MSACPC2	Memory Stick® PC Card Adaptor	Info	add to cart
Batteries:			
NPFC10	InfoLithium® FC Rechargeable Battery	Info	add to cart
Chargers:			
BCVC10	AC Quick Battery Charger	Info	add to cart

Cases:

LCSCP1	Soft carrying case	info	add to cart
LCMPX	Semi-soft carrying case	info	add to cart

Accessory Kits :

ACCCSP	Starter Kit (LCS-CP1/NP-FC10/MSA-32A)	info	add to cart
--------	---------------------------------------	----------------------	-----------------------------

Lights and Flashes:

HVLM20	Marine Video Light	info	add to cart
--------	--------------------	----------------------	-----------------------------

Tripods:

VCTTK1	Small Tripod 2.75" tall	info	add to cart
VCTR610	Lightweight Tripod 21.5"-62"	info	add to cart

Other:

MPKP5	Marine Pack for the DSC-P3 and DSC-P5 (underwater housing)	info	add to cart
VFMP5K	Filter Kit for MPK-P5	info	add to cart
VCTMP1K	Bracket Kit for HV-ML20	info	add to cart