

Garant S IP 44 cable reel 40 m H07RN-F 3G1,5

For constant use outdoors, IP 44.



**MADE IN
GERMANY**



Product number

1198340

EAN

4007123021598

DESCRIPTION

- Reel body made from rust-resistant and galvanised sheet steel fitted to a particularly sturdy galvanised steel tube frame.
- Innovative and ergonomic cable guide handle „cable pilot“ for perfect cable-management during winding. Handle commutes on both sides and allows easy carrying and cable storage. For right and left handed easy to rewind.
- Rotary handle for comfortable rolling up.
- RN cable is very robust, oil resistant and especially suited for professional use and on site.
- 3 water-jet protected earthed socket outlets with self-closing protective caps.
- Thermal cut-out protection, indicator shows overheating or overloading.

TECHNICAL DATA

Cable quality	Rubber-Neoprene	Plug system socket	Type E (FR)
Cable length	40 m	Plug system plug	Type E and F (Protective contact with earth hole)
Cable designation	H07RN-F 3G1,5	Max. current carrying capacity	16 A
Cable colour	black	Nominal input voltage	230 V
Reel diameter	290 mm	Degree of protection (IP)	IP44
Plug system CEE socket	Without		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	8 kg
Weight of product (without packaging)	8 kg	Dimension LxWxH (incl. packing)	19.5 cm x 29 cm x 37 cm
Dimension LxWxH (without packing)	19.3 cm x 28.7 cm x 36.6 cm		