


SAUTER TI-D

KERN

Lever operated test stand for hardness testing with base plate made of glass



Product information

GTIN/EAN number	4045761140240
Trade number	90248000
REACH classification	no prohibited substances

Pictograms

STANDARD



Category

Brand	Sauter
Product category	Hardness testing
Product group	Manual Shore test stand
Product family	TI

Measuring System

Hardness scales	Shore D
Test force Hardness measurement	50 N

Construction

Dimensions completely mounted (W×D×H)	150×200×400 mm
Base plate diameter (Ø)	75 mm
Material housing	stainless steel
Test object height [Max]	60 mm
Traverse distance with lever movement / release [Max]	15 mm

Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	355×255×180 mm
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	10 kg
Shipping weight	9,5 kg
Shipping volume weight	3,3 kg