

M18 ONEFHIWF34-O

M18 FUEL™ ONE-KEY™ ¾" HIGH TORQUE IMPACT WRENCH WITH FRICTION RING

The M18 FUEL™ high torque impact wrench with ONE-KEY™ technology delivers 1627 Nm of fastening torque in a compact size of 213 mm, which gives more access in tight spaces

The 4 -Mode DRIVE CONTROL allows the user to shift into four different speed and torque settings to maximise application versatility

Mode 4 bolt removal, provides a maximum nut-busting torque of 2034 Nm then shifts to 750 rpm for outstanding control when removing fasteners

The integrated blow counting sensor enhances the consistent repeatability of the chosen torque setting

ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools.

ONE-KEY™ also features a remote locking functionality. Customisation function allows for precise tool adjustment to application


The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

¾" friction ring reception

Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



No load speed (rpm)	0-800/0-1300/0-1800/0-1800
Impact rate (ipm)	0-850/0-1850/0-2400/0-2400
Tool reception	¾" square
Max. torque (Nm)	
Nut busting torque (Nm)	0-702/0-1138/0-1627/0-2034
Weight with battery pack (EPTA) (kg)	3.5 (M18 B5)
Kit included	, No charger supplied, No kitbox or bag supplied
Article number	4933499164