

Product data sheet

179 N XL-7

EAN-No. 4000896215164



L x W x H: 959 mm x 518 mm x 1020 mm · 7 Drawers total



Application:

Efficient, mobile organisation of tools

- Tool trolley
- 5 flat and 2 high drawers

Work surfaces

- Much larger storage and work areas in stainless steel
- Fully sealed work surface protects inside of trolley from leaking liquids
- Interfaces integrated in the work area for accessories such as laptop holders and top modules
- Stainless steel work surface
- Extra protection through high-quality plastic end caps

Body / pull-handle

- Extremely robust design thanks to double-walled construction
- Complete welded construction of the entire body for tough daily workshop use
- Optimised, yielding edge protection on all four corners with real impact protection thanks to internal damping concept
- Ergonomically optimised pull handle for better manoeuvrability
- Brushed stainless steel handle

Locking concept

- Lateral cylinder lock (replaceable) with two folding keys (adjustable, including serial number) protects the lock and key from damage
- Highly secure closing system with central locking technology for optimum protection of your property
- 2-stage locking
 - Central locking, lockable with cylinder lock and 2 folding keys
 - Mutual drawer locking for minimum tilting risk

Drawer concept

- Self-closing and reciprocal locking of the drawers prevents unwanted opening
- 100% sliding-out with ball-bearing telescopic slides
- Drawer design for optimum use of the interior
- Drawer fronts for optimised handling
- Dirt-resistant drawer coating for easy cleaning

High performance chassis

Product data sheet

179 N XL-7

EAN-No. 4000896215164



- Large wheels with high loading capacity, precision ball bearing and dual rounded rim in the pivot bearing, easy manoeuvrability, even with high dynamic load
- 2 swivel castors with dual brake:
 - Braked castors prevent rolling away
 - Braked swivel bearings prevent the swivel castors from turning, e.g. on inclined surfaces
- Protective ring prevents dirt and threads from getting in
- “Non-marking” castors leave no marks on the floor and enable smooth running
- Total loading capacity (dynamic): 750 kg
- Loading capacity (static): 1000 kg
- Loading capacity per drawer: 50 kg
- Colour: HAZET blue
- Made in Germany
- Dimensions: 959 mm x 518 mm x 1020 mm
- Net weight: 105.7 kg
- Drawers, flat: 5x 81 x 696 x 398 mm
- Drawers, high: 2x 166 x 696 x 398 mm
- (Drawer) size for plastic drawer insert: 4/3+
- Worktop: Stainless steel
- Number of fixed castors: 2 (Ø 125 mm)
- Number of swivel castors: 2 (Ø 125 mm)

Order Number

179 N XL-7