



M12 FUEL™

M12 FCS442-502X

M12 FUEL™ SUB COMPACT CIRCULAR SAW

Redesigned brushless POWERSTATE™ motor for up to 25% increase in performance when combined with MILWAUKEE® M12™ HIGH OUTPUT™ batteries

Magnesium shoe reduces weight and maximises durability

Integrated dust blower keeps cut line clear

LED light illuminates the cut line for better visibility

Kitted with a DEK26 dust extraction adapter for a cleaner working environment

Maximum cutting depth of up to 46 mm with impressive power for a sub compact circular saw to cut through solid wooden materials at full depth

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M12™ batteries



REDLITHIUM™



No load speed (rpm)	3,850
Max. cutting depth 90° (mm)	46
Max. cutting depth 45° (mm)	32
Blade diameter (mm)	140
Bore size (mm)	20
Weight with battery pack (EPTA) (kg)	2.4 (M12 HB5)
Kit included	2 x M12 HB5 Battery packs, C12 C Charger, HD Box
Article number	4933493489