

M18 FDGRB-O

M18 FUEL™ BRAKING DIE GRINDER WITH SLIDE SWITCH

- Delivering corded performance similar to a 1200 W grinder
- Spindle lock - increased productivity by reducing the need of 2 wrenches
- RAPIDSTOP™ stops all accessories in under the 2 seconds
- Lower angle of battery slot for better balance & ergonomics compared to previous model
- Universal reception to fit both, 6 and 8 mm accessories
- Slim handle design
- Removable dust screen to prevent debris entrance, prolonging motor life
- Rubber front provides most comfortable handling
- Line-lock-out function to prevent automatic start up
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



No load speed (rpm)	27,000
Collet capacity (mm)	6 & 8
Max. grinding accessories diameter (mm)	50
Weight with battery pack (EPTA) 2.0 (M18 B5) (kg)	
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933480952