


NATR40-PP

Galet de roulement

Yoke type track rollers NATR...-PP-A, single row needle roller bearings with particularly thick-walled outer ring, needle roller and cage assembly and an inner ring, axial guidance of outer ring is provided by the plastic axial plain washers and contact washers, three-stage sealing by plastic axial plain washer on both sides

Information technique



Votre alternative produit actuelle

|                             |     |                               |
|-----------------------------|-----|-------------------------------|
| joint                       | PP  | Joint frottant des deux côtés |
| profile bague extérieure    | IOP | Optimized INA-profile         |
| dispositif de lubrification | IR  | Via inner ring                |

dimensions principale & données de performance

|                     |           |                                                         |
|---------------------|-----------|---------------------------------------------------------|
| d                   | 40 mm     | Alésage                                                 |
| D                   | 80 mm     | Diamètre extérieur                                      |
| B                   | 32 mm     | Largeur, bague intérieure                               |
| C <sub>r w</sub>    | 32.500 N  | Charge dyn. de base, radiale                            |
| C <sub>0r w</sub>   | 59.000 N  | Charge stat. de base, radiale                           |
| C <sub>ur w</sub>   | 8.400 N   | Limite à la fatigue, radiale                            |
| n <sub>D G</sub>    | 850 1/min | Vitesse pour une lubrification à la graisse             |
| F <sub>0r per</sub> | 59.000 N  | Charge radiale statique admissible                      |
| F <sub>r per</sub>  | 59.000 N  | Charge radial dynamique admissible sur bague extérieure |
| ≈m                  | 0,796 kg  | Poids                                                   |

Dimensions

|                  |        |                                      |
|------------------|--------|--------------------------------------|
| C                | 30 mm  | Largeur, bague extérieure            |
| d <sub>2</sub>   | 66 mm  | Diamètre extérieur rondelle de butée |
| r <sub>min</sub> | 1,1 mm | Dimension minimum de chanfrein       |



### Caractéristiques

---



Effort radial



Lubrification à vie, sans entretien



Lubrification à la graisse



Étanche des 2 côtés