



7-DRAWER TROLLEY COMPOSITION OF 302 TOOLS IN FOAM MODULES FOR TROLLEYS

417-302MM

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>


Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:45





DESCRIPTION

MODULES MOUSSE



7-DRAWER TROLLEY COMPOSITION OF 302 TOOLS IN FOAM MODULES FOR TROLLEYS

New tool compositions in 5, 6, and 7 complete drawers, with quality tools, combining essential tools and specific tools for industrial and automotive maintenance.

Available in 5, 6, 7, or 9 drawer tool chests. 3 new compositions carefully designed.

Each configuration has been designed to meet the real needs of professionals.

BECAUSE LISTENING TO YOU MEANS PROVIDING EXACTLY WHAT YOU NEED.

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:45



SPECIFIC DATA

Designation	WORK BENCH 41 - 7 DRAWERS - RED - 302 TOOLS
Sales reference	417-302MM
Weight (kg)	119.5
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

Toolset



x 1

Large volume tool trolley- 41 series - new generation - 7 drawers
417H



x 1

Selection of tightening tools - foam module 3/3
CP-138PM



x 1

Screw driving bits ph + hex
E-900J10
Ref : E-900J10



x 1

Screw driving bits pz +tx
E-910J10
Ref : E-910J10



x 1

Screw driving bits fte +txr
E-920J10
Ref : E-920J10



x 1

3/8" sliding handle
J-120
Ref : J-120

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:45



	x 1	1/2" site ratchet with lever reversion J-157B Ref : J-157B
	x 2	Straight 3/8" extensions J-2... Ref : J-208 - J-210
	x 1	3/8" joint J-240 Ref : J-240
	x 17	3/8" short hexagonal sockets in mm JH-... Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22
	x 2	LONG SOCKET 6-FLAT 3/8" 28 MM JHL-... Ref : 16 - 21
	x 5	3/8" sockets for Torx® head JTX-... Ref : 10 - 11 - 12 - 14 - 16
	x 15	1/4" short hexagonal key socket (mm) R-...Douilles_1/4_MM Ref : 3,5 - 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15
	x 1	1/4" sliding handle R-120 Ref : R-120
	x 1	Site 1/4" ratchet R-157B Ref : R-157B
	x 2	Straight 1/4" extensions R-21... Ref : R-210 - R-211
	x 1	Flexible 1/4" extension R-220 Ref : R-220
	x 1	Fitted 1/4" extension R-225 Ref : R-225
	x 1	1/4" joint R-240 Ref : R-240
	x 1	1/4" bit holder socket RD-1 Ref : RD-1

	x 6	1/4" single-piece screwdriver sockets for hollow hexagonal screws RS-... Ref : 3 - 4 - 5 - 6 - 7 - 8
	x 1	Sets of 6 screwdriver sockets 1/4" for 6-flat socket head screws on storage rack RS-J6R Ref : RS-J6R
	x 1	Set of 8 screwdriver sockets 1/4" for Torx® imprint on storage rack RT-J8R Ref : RT-J8R
	x 5	1/4" sockets for Torx® head RTX-... Ref : 4 - 5 - 6 - 7 - 8
	x 1	1/2" sliding locking handle S-120 Ref : S-120
	x 1	1/2" site ratchet with lever reversion S-157B Ref : S-157B
	x 1	Straight 1/2" extensions S-2... Ref : S-215
	x 1	1/2" joint S-240 Ref : S-240
	x 18	1/2" short hexagonal sockets in mm SH-... Ref : 10 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 - 27 - 30 - 32
	x 5	1/2" long bi-hexagonal sockets in mm SL-...Douilles_MM Ref : 14 - 15 - 17 - 19 - 22
	x 3	1/2" sockets for Torx® head STX-... Ref : 18 - 20 - 24
	x 1	3/3 FOAM MODULE 12 PLIERS CP-12MM
	x 1	Polished chrome-plated universal pliers with spring 204-R...G Ref : 204-R18G
	x 1	Mechanic's diagonal chrome-plated cutting pliers with spring 232-R...G Ref : 232-R18G

	x 1	Straight half-round nose pliers, polished chrome-plate 237-...G Ref : 237-20G
	x 1	Polished chrome-plated angled half-round nose pliers with spring 239-R20G
	x 1	Mat chrome-plated straight nose outer circlips pliers 195-...A Ref : 195-17A
	x 1	Mat chrome-plated 90° elbowed nose outer circlips pliers 196-...A Ref : 196-17A
	x 1	Burnished finish straight nose inner circlips pliers 190-...A Ref : 190-17A
	x 1	Mat chrome-plated 90° elbowed nose inner circlips pliers 191-...A Ref : 191-17A
	x 1	High-capacity lock grip pliers 212-25
	x 1	Crimping pliers 241-42
	x 1	Polished chrome-plated stacked-branch multigrip pliers 209-25B
	x 1	Mechanic's end nippers 229-... Ref : 229-25



x 1

MODM 3/3 88 SCREWDRIVER+WRENCHES MA.
CP-88MM

	x 1	Flexible screwdriver 6 mm 23-... Ref : 7 mm
	x 1	Ratchet telescopic screwdriver with magnetic bit holder T-PE
	x 9	Rack of 9 male 6-flat keys with spherical head in mm 67-AR9A Ref : 1,5 - 2 - 2,5 - 3 - 4 - 5 - 6 - 8 - 10 mm

	x 9	Rack of 9 Torx® male keys 66-R9A Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40
	x 9	Torx® S1 round blade screwdriver T-...X Ref : T8 - T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40
	x 2	Testing screwdriver 268-... Ref : 6-24V et 100-500V
	x 3	SCREWDRIVER ELECTRICIAN INSULATED 1000V ZTC-...E Ref : N°2 - N°3 - N°4
	x 2	SCREWDRIVER PHILLIPS® INSULATED 1000V ZTC-...P Ref : N°1 - N°2
	x 1	Electrician's S1 round blade slotted head screwdriver T-...E Ref : 4x100 mm
	x 3	Mechanic's S1 round blade slotted head screwdriver T-...M Ref : 5,5x100 - 6,5x100 - 8x150 mm
	x 3	Phillips® S1 round blade screwdriver T-...P Ref : N°1 - N°2 - N°3
	x 1	Phillips® S1 round blade tom thumb screwdriver T-...P_Tom_pouce Ref : N°2
	x 1	Electrician's S1 round blade tom thumb slotted head screwdriver T-...E_Tom_pouce Ref : 6,5x35 mm
	x 30	31-piece screwdriver bit set E900-J30B
	x 1	3/3 FOAM MOD 24 STRIK TOOLS CP-24MM
	x 1	SAMSOPLUS® riveting hammer, three-material handle 310-...TM Ref : 32 mm
	x 1	Mallets with interchangeable tips 320-...D Ref : 32 mm



x 1

Short tape measures with two-material casings

UB-...N

Ref : 2 m



x 1

Slide callipers with 1/2"0 mm precision

710-P-8



x 1

Plastic body scriber

665-11



x 6

Short drift punches

7-C...A

Ref : 1,9 - 2,9 - 3,9 - 4,9 - 5,9 - 7,9 mm



x 1

Knife with retractable blade

378-7



x 5

Set of 5 helix pullers

761-C-5



x 1

Fitted flat hand file

LPM-...E

Ref : 250 mm



x 1

Fitted round files

LR-...-E

Ref : 250 mm



x 1

Fitted half-round files

LDR-...-E

Ref : 250 mm



x 2

Constant section chisels with comfortable handle

3-...-G

Ref : 175 - 200 mm



x 1

Punch 10 mm

8N-...A

Ref : 8 mm



x 1

3/3 FOAM MOD 40 WRENCHES

CP-40MM



x 19

Extra-thin combination wrench

50N-...

Ref : 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 - 24 mm



x 9

Set of 9 multi-nut inch / metric ratchet combination spanners

50-HCJ9

Ref : 10 - 11 - 12 - 13 - 14 - 16 - 17 - 18 - 19 mm



x 8

Set of 8 offset ring wrenches in mm
105-J8D



x 4

Torx® polygonal straight wrench
9T-...
Ref : E6xE8 - E10xE12 - E14xE18 - E20xE24 mm

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:45

