

KERN 356-86

KERN

Individual weight, OIML Class M2, 5 kg, Block, cast iron lacquered



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M2
Product family	356

Measuring System

Test weight - nominal value	5 kg
Test weight - volume uncertainty (cm ³)	59,512
Weight OIML class	M2
Test weight - volume (cm ³)	704,2254
Permissible tolerance according to OIML (+/-)	800 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2300
Test weight - Density (kg/m ³)	7100
Test weight - Density uncertainty (kg/m ³)	600

Construction

Shape weight	Block
Dimensions weight (W×D×H)	150×75×84 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-643
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	150×75×84 mm
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	5,0 kg
Shipping weight	5 kg
Shipping volume weight	0,2 kg

Optional cases

Case - Aluminium article number	346-060-600
---------------------------------	-------------

Product information

GTIN/EAN number	4045761248281
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

