



# VDE Diagonal Cutter 160mm

## VDE DIAGONAL CUTTERS

- VDE (DIN EN/IEC 60900) certified tools. Tested to 10,000 volts and guaranteed to 1,000 volts. Tested against cold to -40°.
- Steel blades are fully forged, hardened and tempered for best durability. Grey titanium surface finish is non reflective and ensures maximum corrosion resistance.
- Induction hardened cutting edges to cut even the hardest of materials.
- Precision machined joint for maximum power transmission with optimum leverage for easy and effortless work.
- Ergonomic grip with softgrip for comfortable handling and good grip.



|                                                          |            |
|----------------------------------------------------------|------------|
| Article Number                                           | 4932464567 |
| Capacity [mm]                                            | -          |
| Capacity Pipe [Max. Ø mm]                                | -          |
| Cutting capacity in cable Al and Cu [Max. Ø mm]          | 11         |
| Cutting capacity in hard wire 1800N/mm² [Max. Ø mm]      | 2          |
| Cutting capacity in soft wire 220N/mm² [Max. Ø mm]       | 6          |
| Cutting capacity in very hard wire 2300N/mm² [Max. Ø mm] | -          |
| Length (mm)                                              | 160        |
| Pack quantity                                            | 1          |
| Total length (mm)                                        | 160        |