

KERN 337-15

KERN

Individual weight, OIML Class F2, 20 kg, Knob, stainless steel fine turned



Article number for guaranteed plus-deviation 921-445

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	128×128×230 mm
Shipping method	Parcel service
Net weight approx.	20 kg
Gross weight approx.	20 kg
Shipping weight	20 kg
Shipping volume weight	0,8 kg

Optional cases

Case - Aluminium article number	317-150-600
Case - Wood article number	337-150-200

Product information

GTIN/EAN number	4045761006607
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML F2
Product family	337

Measuring System

Test weight - nominal value	20 kg
Test weight - volume uncertainty (cm ³)	31,25
Weight OIML class	F2
Conformity assessment possible	no
Test weight - volume (cm ³)	2500
Permissible tolerance according to OIML (+/-)	300 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	6400
Test weight - Density [Max] (OIML)	10700
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction

Shape weight	Knob
Dimensions (Ø×H)	128×230 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-445
--------------------------------------	---------