

KERN 357-05

KERN

Individual weight, OIML Class M2, 20 g, Knob, stainless steel fine turned



Category	
Brand	KERN
Product category	Individual weight
Product group	OIML M2
Product family	357

Measuring System	
Test weight - nominal value	20 g
Test weight - volume uncertainty (cm ³)	0,0482
Weight OIML class	M2
Test weight - volume (cm ³)	2,381
Permissible tolerance according to OIML (+/-)	8 mg
OIML-compliant	✓
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction	
Shape weight	Knob
Dimensions (Ø×H)	13×21 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

Services (optional)	
Article number for DAkkS calibration	962-635

Packing & Shipping	
Delivery time	1 d

Dimensions packaging (W×D×H)	24×24×51 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg
Shipping volume weight	0,1 kg

Optional cases	
Case - Plastic article number	347-050-400
Case - Aluminium article number	317-050-600
Case - Wood article number	337-050-200

Product information	
GTIN/EAN number	4045761288966
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

