

KERN 337-131

KERN

Individual weight, OIML Class F2, 5 kg, Check weight, stainless steel fine turned



Article number for guaranteed plus-deviation 921-443

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	136×136×132 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	10 kg
Shipping weight	10 kg
Shipping volume weight	0,5 kg

Optional cases

Case - Wood article number 337-131-200

Product information

GTIN/EAN number	4045761473898
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML F2
Product family	337

Measuring System

Test weight - nominal value	5 kg
Test weight - volume uncertainty (cm ³)	15,625
Weight OIML class	F2
Test weight - volume (cm ³)	1250
Permissible tolerance according to OIML (+/-)	80 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	7390
Test weight - Density [Max] (OIML)	10700
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction

Shape weight	Check weight
Dimensions (Ø×H)	136×132 mm
Material	stainless steel fine turned
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-443
--------------------------------------	---------