

ALEV 160/20K

Heavy duty wheel, with 'Blickle EasyRoll' elastic solid rubber tyres, with aluminium wheel centre

EAN 4047526234102

ID 234104

Customs tariff number 87169090



Tyre:

- high-quality elastic solid rubber "Blickle EasyRoll" in smooth rolling quality, hardness 65 Shore A
- very good operational comfort
- very good floor preservation, low-noise operation
- low rolling resistance
- colour black
- vulcanised onto the wheel centre

Wheel centre:

- die-cast aluminium

Other features:

- high chemical resistance to many aggressive substances, except oils
- operating temperature: -20 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +60 °C



Technical data:

Wheel Ø (D)	☉	160 mm
Wheel width	⌞	50 mm
Load capacity at 4 km/h	⚖	400 kg
Load capacity at 6 km/h	⚖	320 kg
Load capacity at 10 km/h	⚖	200 kg
Load capacity (static)	⚖	1,000 kg
Bearing type	⦿	ball bearing
Axle bore Ø (d)		20 mm
Hub keyway (T1)	⌘	60 mm
Temperature resistance min		-20 °C
Temperature resistance max		80 °C
Tread and tyre hardness		65 Shore A
Unit weight	⚖	1.1 kg
Non-marking	✗	
Non-staining	✗	
Antistatic	⚡	✗
ESD	✗	
Electrically conductive	⚡	✗
Corrosion-resistant	✗	
Heat-resistant	🔥	✗
Suitable for autoclaves	✗	

Tread and tyre hardness

■ ■ ■ ■ ■ 65 Shore A

Rolling resistance

■ ■ ■ ■ ■ very good

Wear resistance

■ ■ ■ ■ ■ good

Operating noise / floor surface preservation

■ ■ ■ ■ ■ very good

