



FACK2SBpm



FACK4Bpm



FKFBpm



KBNC1275BPM



KBNC50Bpm



KCF3GBpm



KCHDBpm



KCK66Bpm



KCUAA2Bpm



KCUABBpm



KOLADXBpm



KOLMMDXBpm



KOLSMDXBpm



KSH66Bpm



SACK3SBpm



SACK4Bpm



SEKjeBpm



SGACK2SBpm



SGACK902SBpm



SGKSjeBpm



SGKSLJBpm



SKFBpm



SKmcBpm



SLJBpm



SGKctBpm



KAPMBfni



KAPMkpk



KAPMkpk2



SGACK90Bpm



SGKSbtBpm



FFPM16MC



FFPM16



KUCC20Bpm

Code	Description	Dimensions - Weight (L x W x H mm)	Link to Keystone's Specification	EAN Numbers
FACK2SBpm	Category 5e female to female coupler, shielded	29.7 x 19 x 35 – 19.5g	FACK2S	5055386509390
FACK4Bpm	Category 5e unshielded compact coupler	29.5 x 19 x 35 – 8.5g	FACK4	5055386509406
FKFBpm	Category 5e tool-less IDC socket, unshielded	37 x 19 x 35 – 8.5g	FKF	5055386509413
KBNC1275Bpm	BNC coupler Ultra HD 75 ohm 12Ghz	32.5 x 19 x 35 – 12.5g	KBNC1275	5055386509468
KBNC50Bpm	BNC 50-ohm female to female coupler	32.5 x 19 x 35 – 18.5g	KBNC50	5055386509475
KCF3GBpm	3G F connector female to female coupler	25.5 x 19 x 35 – 8.5g	KCF3G	5055386509857
KCHDBpm	HDMI female to female coupler	19.8 x 19 x 35 – 10.5g	KCHD	5055386509482
KCK66Bpm	RJ12 6p6c coupler	26.5 x 19 x 35 – 6.5g	KCK66BKne	5055386509703
KCUAA2Bpm	USB2 A female to A female coupler	35.5 x 19 x 35 – 10.5g	KCUAA2	5055386509499
KCUABBpm	USB2 A female to B female adaptor, reversible	34.4 x 19 x 35 – 10.5g	KCUAB	5055386509505
KOLADXBpm	Fibre female to female coupler, LC APC to LC APC, single mode duplex	35 x 19 x 35 – 6.5g	KOLADX	5055386509512
KUCC20Bpm	USB C female keystone to C male 20cm tailed lead	200 x 33.67 x 16.30 – 34g	KUCC*20	5055386512918
KOLMMDXBpm	Fibre female to female coupler LC to LC, multi mode duplex	33 x 19 x 35 – 6.5g	KOLMMDX	5055386509529
KOLSMDXBpm	Fibre female to female coupler LC to LC, single mode duplex	34 x 19 x 35 – 6.5g	KOLSMDX	5055386509536
KSH66Bpm	RJ12 6p6c socket	36.4 x 22.8 x 35 – 8.5g	KSH66	5055386509543
KUA2Bpm	USB2 A Screw Termination Socket	28.4 x 19 x 35 – 8.5g	KUA2	5055386509550
SACK3SBpm	Category 6 female to female coupler, shielded	30 x 19 x 35 – 20.5g	SACK3S	5055386509574
SACK4Bpm	Category 6 unshielded compact coupler	30 x 19 x 35 – 8.5g	SACK4	5055386509581

SEKjeBpm	Category 8 socket	41.6 x 19 x 35 – 30.5g	SEKje	5055386509598
SGACK2SBpm	Category 6A female to female coupler, shielded	29.7 x 19 x 35 – 19.5g	SGACK2S	5055386509604
SGACK902SBpm	Category 6A female to female coupler, w/rear outlet 90° to front outlet, shielded (suitable for Cat 6 or Cat 5e)	36.1 x 19 x 35 – 12.5g	SGACK902s	5055386509611
SGACK90Bpm	Category 6A female to female coupler, w/rear outlet 90° to front outlet Unshielded	36.1 x 19 x 35 – 8g	SGACK90	
SGKSjeBpm	Category 6A shielded socket	37.8 x 19 x 35 – 24.5g	SGKSje	5055386509628
SGKSLJBpm	Category 6A STP tool-less locking socket	38.75 x 19 x 35 – 20.5g	SGKSLJ	5055386509840
SGKSbtBpm	Category 6A contractor grade shielded socket	47 x 24 x 18mm – 24g	SGKSbt	5055386512765
SKFBpm	Category 6 tool-less IDC socket, unshielded	38 x 19 x 35 – 10.5g	SKF*	5055386509635
SKmcBpm	Category 6 IDC socket, LSA-Plus and 110 type termination, unshielded	34 x 19 x 35 – 8.5g	SKmc	5055386509642
SLJBpm	LOKJAC Category 6 tool-less locking socket	36 x 19 x 35 – 8.5g	SLJ	5055386509659
SGKctBpm	Category 6A Toolless UTP socket	17 x 19.5 x 37.90 – 10g	SGKctbk	5055386511416
KAPMBfnl	Low profile black panel mount adaptor	11 x 19 x 35 – 2.5g	KAPMBfnl	5055386509420
KAPMBfnl#20	Low profile black panel mount adaptor in bags of 20	25 x 180 x 110 – 100g	KAPMBfnl	5055386509437
KAPMkpk	Low profile black panel mount blank	11 x 19 x 35 – 2.7g	KAPMkpk	5055386509444
KAPMkpk#20	Low profile black panel mount blank in bags of 20	25 x 180 x 110 – 100g	KAPMkpk	5055386509451
KAPMkpk2	Clip-in blank for flexible applications, allows for installation of connectors	20.1 x 19 x 35 – 3g	KPKbk	5055386509697
FFPM16, FFPM16CM	Panel mount 16 port-panel available both with, and without cable management.	482 x 14 x 44.2 – 364g, 482 x 68.4 x 44.2 – 474g	FFPM16 , FFPM16CM	5055386508805, 5055386508812

More Information:

TUK's Low Profile Panel Mount Range offers a wide variety of audio, video and data connectors which can easily be mounted into panels of virtually any thickness.

Each connector is supplied as a kit. Kit includes coupler/connector, panel mount adaptor, and 2 pairs of black steel flat head screws (2 x M3s for European installations, 2 x 4:40s for US installations).

The Low Profile Black adaptor KAPMBfml is durable and ensures easy mounting (into standard cut-out) – can be purchased on its own in packs of 20 pcs.

All connectors are made to relevant standards. Category 6 and 6A connectors are produced, for example, to FCC68 and to TIA/EIA 568B and have an insertion life of > 750 mating cycles. All products are CE compliant (i.e including ROHS and REACH)

13th November 2024

Rear View



FACK2SBpm



FACK4Bpm



FKFBpm



KBNC1275BPM



KBNC50Bpm



KCF3GBpm



KCHDBpm



KCK66Bpm



KCUAA2Bpm



KCUABBpm



KOLADXBpm



KOLMMDXBpm



FFPM16MC



FFPM16





KOLSMDXBpm



KSH66Bpm



SACK3SBpm



SACK4Bpm



SEKjeBpm



SGACK2SBpm



SGACK902SBpm



SGKSjeBpm



SGKSLJBpm



SKFBpm



SKmcBpm



SLJBpm



SGKctBpm



KAPMBfml



KAPMkpk



KAPMkpk2

TUK Ltd, Unit 4, Wimbledon Stadium Business Centre, Riverside Road, London SW17 0BA

Tel: +44 (0) 20 8946 6688 Fax: +44 (0) 20 8879 7410 Email: sales@tuk.co.uk Website: www.tuk.co.uk

TUK follows a policy of continuous improvement. All information is correct at the time of printing but may be subject to change without prior notification. Please contact TUK for formal confirmation of current specification. HDMI and LSA-Plus are registered trademarks of HDMI Licensing and Krone (UK) Technique Ltd respectively, whose rights are acknowledged. is a registered trademark of TUK Limited.