



PRODUCT-DETAILS

NVNV-P112

FTNG STR PG11 NW12 PA6/BR IP68 BLK



General Information	
Extended Product Type:	NVNV-P112
Product ID:	7TAA292150R0678
EAN:	7630030255847
Catalog Description:	FTNG STR PG11 NW12 PA6/BR IP68 BLK
Long Description:	VNV Connector Straight, PG Metal Thread for IP68 - Thread PG 11, Fits to Conduit Size NW/Metric 12/16, Color Black
Display Name:	NVNV-P112

Eco Transparency	
Environmental Product Declaration - EPD: 9AKK108471A8618	

Additional Information	
Product Main Type:	PMA Flexible Cable Protection
Application:	Use In Railway Vehicle and Heavy Machine Construction

Product Type: Connectors-Straight

Ordering

EAN: 7630030255847

UPC: 786209964137

Technical

Number of Batteries: 0

Color: Black

Material: Polyamide 6 with Nickel Plated Brass Threads

Size: NW12 , PG11 Thread

Environmental

WEEE Category: Product Not in WEEE Scope

Container Information

Package Level 1 Units: 50 EA

Package Level 1 EAN: 7630030255847

Package Level 1 Height: 0 mm
0 in

Package Level 1 Depth / Length: 0 mm
0 in

Package Level 1 Width: 0 mm
0 in

Certificates and Declarations

Data Sheet, Technical Information: NVNV-P112

Instructions and Manuals: NVNV-P112

Declaration of Conformity - CE: 9AKK107680A0674

External Classifications and Standards

ETIM 8: EC001176 - Screw connection for corrugated plastic hose

ETIM 9: EC001176 - Screw connection for corrugated plastic hose

UNSPSC: 39121311

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

