

KERN BIC-A07

KERN

Pair of base plates to fix the weighing bridge to the floor



Pictograms

STANDARD



Category

Brand	KERN
Product category	Balance
Product group	Base plate

Construction

Dimension (W×D×H)	200×200×10 mm
Dimension housing (W×D×H)	100×287×3 mm
Material	steel, powder-coated
Material platform	steel, lacquered
Material load cell(s)	steel
Material	steel (1.4305)

Environmental conditions

Ambient temperature [Min]	-20 °C
Ambient temperature [Max]	60 °C

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	200×200×10 mm
Shipping method	Parcel service
Net weight approx.	0,75 kg
Gross weight approx.	0,80 kg
Shipping weight	0,785 kg
Shipping volume weight	0,1 kg

Product information

GTIN/EAN number	4045761193291
Trade number	84239010
REACH classification	no prohibited substances