

P 403/20-90R

Wheel, with pneumatic tyre, with pressed steel rim

EAN 4047526254841
ID 254847
Customs tariff number 87169090



Tyre:

- pneumatic tyre, zig-zag profile, hardness 60 Shore A
- 2-ply rating, with inner tube
- maximum operational comfort
- excellent floor preservation, particularly quiet operation
- colour black

Rim:

- pressed steel
- with welded tubular steel hub
- lacquered, colour silver

Other features:

- chemical resistance to many aggressive substances, except oils
- operating temperature: -25 °C to +50 °C
- the wheel and tyre dimensions provided here apply to new tyres that are not bearing a load. Their width and diameter may change when they are in use.
- speeds up to 16 km/h possible for wheels with ball bearing and reduced load capacity

Technical data:

Wheel Ø (D)		400 mm
Wheel width		100 mm
Tyre dimensions		4.00-8
Ply rating		2
Load capacity at 4 km/h		250 kg
Load capacity (static)		250 kg
Tyre pressure		2.0 / 30 bar / psi
Bearing type		roller bearing
Axle bore Ø (d)		20 mm
Hub keyway (T1)		90 mm
Profile		zig-zag profile
Temperature resistance min		-25 °C
Temperature resistance max		50 °C
Tread and tyre hardness		60 Shore A
Unit weight		3.1 kg
Non-marking		×
Non-staining		×
Antistatic		×
ESD		×
Electrically conductive		×
Corrosion-resistant		×
Heat-resistant		×
Suitable for autoclaves		×



Tread and tyre hardness

 60 Shore A

Rolling resistance

 good

Wear resistance

 satisfactory

Operating noise / floor surface preservation

 excellent

