



Hinge 8 40x40, heavy-duty with Clamp Lever



REACH RoHS

The Hinge connects profiles at any angle up to 180°. It can be used as a hinge (adjustment range $\pm 90^\circ$) or rigid angle element. The connection is made on the face side or with the matching t-slot nut. The Hinges with Clamp Lever can be locked in position or released. Particularly suitable for adjustable holders, swivel-type arms for Parts Containers and other similar equipment.



Scope of Delivery

2 hinge halves, die-cast zinc, RAL9006 white aluminium
4 fixing elements, die-cast zinc, bright zinc-plated
1 Thread bush M8, St, zinc-plated
1 Bush liner, St, zinc-plated
1 Spacer collar, St
1 Clamp lever M8x40, black

Technical note

[0.0.373.93](#) Please click here for further information!

Properties	
Article number	0.0.373.93
Delivery unit	1 pce.
Weight	410.0 g

Accessoires	
8.0.000.19	Button-Head Screw M8x16, bright zinc-plated
0.0.026.18	T-Slot Nut 8 St M8, bright zinc-plated