

KERN 317-16

KERN

Individual weight, OIML Class E2, 50 kg, Knob, stainless steel polished



Category

Brand	KERN
Product category	Individual weight
Product group	OIML E2
Product family	317

Measuring System

Test weight - nominal value	50 kg
Test weight - volume uncertainty (cm ³)	78,125
Weight OIML class	E2
Test weight - volume (cm ³)	6250
Permissible tolerance according to OIML (+/-)	80 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	7810
Test weight - Density [Max] (OIML)	8210
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction

Shape weight	Knob
Dimensions (Ø×H)	178×298 mm
Material	stainless steel polished
Adjustment method	Polishing

Services (optional)

Article number for DAkkS calibration	962-346
Article number for guaranteed plus-deviation	921-346

Packing & Shipping

Delivery time	30 d
Dimensions packaging (W×D×H)	178×178×298 mm
Shipping method	Freight
Net weight approx.	50 kg
Gross weight approx.	50 kg
Shipping weight	50 kg
Shipping volume weight	1,9 kg

Optional cases

Case - Aluminium article number	317-160-600
Case - Wood article number	317-160-100

Product information

GTIN/EAN number	4045761003828
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

