

操作 器

61-
2101.0/D

分销方
Rs-online



<https://rs-online.eao.com/component/61-2101.0...>

您的产品:



61-2101.0/D 操作器

安装

安装类型: 面板安装

电气特性

静电放电 (ESD) : 11 kV

机械特性

开关动作: 复位 (a) - 自复位

旋转位置: 2位置

开关角度: 42°右

机械寿命: >15 000次交配周期, 50 000 次

操作力: 0.025...0.1Nm 速动开关元件, 0.4 ... 0.16 Nm 慢动开关元件

操作行程: 约 42°

拧紧力矩: 最大 0.5 Nm

重量: 0.009 kg

环境条件

IP保护: IP40后部, 符合EN IEC 60529, 正面为IP67, 符合EN IEC 60529

工作温度: - 25 °C ... + 55 °C

储存温度: - 40 °C ... + 85 °C

证书

REACH: REACH compliant

RoHS:

RoHS compliant

其他

简述:

操作器, 复位 (a) - 自复位


外壳材质:

塑料,符合 UL 94 V0, 阻燃

产品属性:

标准锁 : DOM 311


切换位置:




接线图:




安装开孔:




A = 焊接/插入式端子 2.8 mm x 0.5 mm
C = 螺钉端子




A = 焊接/插入式端子 2.8 mm x 0.5 mm
C = 螺钉端子



A = 焊接/插入式端子 2.8 mm x 0.5 mm
C = 螺钉端子




A = 焊接/插入式端子 2.8 mm x 0.5 mm
C = 螺钉端子



A = 焊接/插入式端子 2.8 mm x 0.5 mm
C = 螺钉端子

外形尺寸:




A = 插入式端子 2.8 mm x 0.5 mm

C = 螺钉端子

E = 慢速开关元件

F = 快动开关元件




A = 插入式端子 2.8 mm x 0.5 mm

C = 螺钉端子

E = 慢速开关元件

F = 快动开关元件



A = 插入式端子 2.8 mm x 0.5 mm

C = 螺钉端子

E = 慢速开关元件

F = 快动开关元件