



Stubby Screwdriver, #2 Phillips, 1-1/2-Inch Round Shank



Full hollow shaft for work on stacked circuit boards or other long bolt applications. Allows for work in close quarters. Internal flanges provide solid, twist-resistant shaft anchor. Cushion-Grip™ handle allows for greater torque and comfort. Handle end is also color coded for easy identification.

Specifications

Tip Type:	Phillips	Magnetic:	No
Tip Size:	#2	Shank Type:	Round
Shank Length:	1.5" (3.8 cm)	Material:	Steel
Insulated:	No	Handle Material:	Rubber
Handle Color:	Black	Overall Length (Inch):	3.438
Overall Length (cm):	8.7	Weight (oz):	1.6
Weight (g):	45		