

Hedge Trimmer LXT®

DUH523

18V • 520 mm

Compact trimmer for home use

A cordless hedge trimmer with a 520 mm blade for gardening. Two-handed safety switches offer added safety and the tool has low noise levels. Vibration-dampened frame.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	2700 min ⁻¹
Length Of Blade	520 mm
Max blade opening	15 mm
Tooth Spacing	26 mm
Continuous Use 18V / 6.0 Ah Battery	150 min
Continuous Use 18V / 3.0 Ah Battery	75 min
Sound Power Level (L _{WA})	84,3 dB(A)
Sound Pressure Level (L _{pA})	77 dB(A)
Noise Uncertainty (K Factor)	2,5 dB(A)
Vibration Level, Hedge Trimming	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²

User benefits

- Specially coated two-way cutting blade with long service life.
- Electric brake for maximum productivity and increased operator safety
- Tool-less blade change for fast blade installation and removal
- 2-hand safety switch
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Anti-vibration structure

Link to product - www.makitauk.com



Related products

■ Optional AC

195769-0

Shear blade 520 mm, Stain-free blade



199450-5

Tool Grease for Hedge Trimmers



452685-2

Blade Cover 520 mm



■ Other

User manual

Parts drawing