

AMY-50-M

~24° medium beam

SPECIFICATION:

Dimensions	Ø 49.9
Height	10.9 mm
Fastening	socket
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
AMY-50-M	Single lens	PMMA	clear		
AMY-50-HLD2-C	Holder C	PC	black		
AMY-50-HLD2-B	Holder B	PC	black		
AMY-50-HLD2-C-WHT	Holder C	PC	white		
AMY-50-HLD2-B-WHT	Holder B	PC	white		



ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C17687_AMY-50-M	690	120	30	9.5
Assembly				
CP19151_AMY-50-M-B2-WHT	510	120	30	8.8
CP19142_AMY-50-M-C2-WHT	510	120	30	8.4
CP19133_AMY-50-M-B2	510	120	30	8.8
CP19124_AMY-50-M-C2	510	120	30	8.4





See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):





LED V10 Gen 8-9
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 26.0° / 48.0°
Efficiency 91 %
LEDs/each optic 1
Light colour/type White
Required components:
F15255_HEKLA-SOCKET-C



Light distribution files




LED V11 HD Gen 8
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 26.0° / 50.0°
Efficiency 91 %
LEDs/each optic 1
Light colour/type White
Required components:
Bender Wirth: 633d Hekla



Light distribution files



LED V13 Gen 8-9
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 31.0° / 60.0°
Efficiency 88 %
LEDs/each optic 1
Light colour/type White
Required components:
F15859_HEKLA-SOCKET-I





Light distribution files

OPTICAL RESULTS (MEASURED):





LED V4 HD Gen 7
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 41.0°
 Efficiency 93 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files





LED V6 HD Gen 7
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 43.0°
 Efficiency 91 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files



LED V8 Gen 8-9
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 46.0°
 Efficiency 92 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A





Light distribution files

OPTICAL RESULTS (MEASURED):





LED V9 HD Gen7
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 25.0° / 46.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
F15859_HEKLA-SOCKET-I



Light distribution files





LED VERO10
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 25.0° / 47.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
F15616_HEKLA-SOCKET-F



Light distribution files



LED Vesta DTW 13mm (21W)
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 30.0° / 57.0°
Efficiency 86 %
LEDs/each optic 1
Light colour/type White
Required components:
C16142_HEKLA-SOCKET-K
Bender Wirth: 491 Typ L8





Light distribution files

OPTICAL RESULTS (MEASURED):





LED Vesta DTW 15mm (33W)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 29.0° / 58.0°
 Efficiency 86 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 491 Typ L8



Light distribution files





LED Vesta RGBW 10mm CSP
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 26.0° / 51.0°
 Efficiency 79 %
 Peak intensity 2.7 cd/lm
 LEDs/each optic 28
 Light colour/type RGBW
 Required components:
 C19950_HEKLA-SOCKET-RZ



Light distribution files



LED Vesta TW 13mm (18W) DP
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 29.0° / 58.0°
 Efficiency 87 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 492 Typ L8





Light distribution files

OPTICAL RESULTS (MEASURED):




LED Vesta TW 15mm DP
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 32.0° / 63.0°
 Efficiency 86 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 482 Typ L8



Light distribution files





LED Vesta TW 6mm DP
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 26.0° / 45.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Bender Wirth: 504 Typ B35L



Light distribution files



LED Vesta TW 6mm DP
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 43.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 504 Typ L8





Light distribution files

OPTICAL RESULTS (MEASURED):





LED Vesta TW 9mm (9W) DP
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 47.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 489 Typ L8



Light distribution files

CITIZEN



LED CLU02x (LES10)
 Ordering code CP19142_AMY-50-M-C2-WHT
 FWHM / FWTM 26.0° / 47.0°
 Efficiency 96 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU02x (LES10)
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 26.0° / 49.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Green Gems: GH27d





Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN



LED CLU02x (LES10)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 48.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN


LED CLU03x
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 29.0° / 58.0°
 Efficiency 87 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

CITIZEN

LED CLU700/701/702/703
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 43.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN



LED CLU7A2/7A3
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 24.0° / 40.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files

CITIZEN


LED CLU7B2
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 24.0° / 39.0°
Efficiency 91 %
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU7L3
Ordering code CP19133_AMY-50-M-B2
FWHM / FWTM 24.0° / 39.0°
Efficiency 93 %
LEDs/each optic 1
Light colour/type White
Required components:
Bender Wirth: 667a Bayonet35




Light distribution files

OPTICAL RESULTS (MEASURED):

CITIZEN



LED CLU7S3
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 24.0° / 40.0°
 Efficiency 91 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Bender Wirth: 667a Bayonet35



Light distribution files





LED CMA1516
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 47.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17436_HEKLA-G2-D



Light distribution files



LED CMA1825
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 27.0° / 54.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15254_HEKLA-SOCKET-B





Light distribution files

OPTICAL RESULTS (MEASURED):





LED CMT14xx
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 25.0° / 48.0°
Efficiency 89 %
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files




LED CMT19xx
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 29.0° / 58.0°
Efficiency 87 %
LEDs/each optic 1
Light colour/type White
Required components:
F17438_HEKLA-G2-I



Light distribution files



LED CXA/B 13xx
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 24.0° / 42.0°
Efficiency 91 %
LEDs/each optic 1
Light colour/type White
Required components:
F17439_HEKLA-G2-J





Light distribution files

OPTICAL RESULTS (MEASURED):





LED CXA/B 15xx
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 25.0° / 46.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
F17436_HEKLA-G2-D



Light distribution files





LED LEDIM/C6
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 26.0° / 46.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
F17438_HEKLA-G2-I



Light distribution files



LED LUXEON 7070
Ordering code CP19133_AMY-50-M-B2
FWHM / FWTM 25.0° / 44.0°
Efficiency 92 %
LEDs/each optic 1
Light colour/type White
Required components:
Bender Wirth: 634a Bayonet35L





Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON CoB 1202/1203
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 46.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files





LED LUXEON CoB 1204HD
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 47.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files



LED LUXEON CoB M02/M03
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 47.0°
 Efficiency 90 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17436_HEKLA-G2-D





Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON CoB S01
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 42.0°
 Efficiency 91 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17439_HEKLA-G2-J



Light distribution files





LED LUXEON Fusion 12-up (20x24)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 47.0°
 Efficiency 83 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS
 Bender Wirth: 442 Typ L8



Light distribution files



LED LUXEON Fusion 21-up (20x24)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 26.0° / 48.0°
 Efficiency 82 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS
 Bender Wirth: 442 Typ L8




Light distribution files

OPTICAL RESULTS (MEASURED):





LED LUXEON Fusion 27-up (20x24)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 29.0° / 55.0°
 Efficiency 80 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 F18158_HEKLA-RZ-LENS
 Bender Wirth: 442 Typ L8



Light distribution files





LED CTM-14 (Tunable White) Gen2
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 29.5° / 57.0°
 Efficiency 86 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 442 Typ L8



Light distribution files



LED CTM-9 (Tunable White)
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 27.0° / 50.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 Bender Wirth: 495 Typ B35L




Light distribution files

OPTICAL RESULTS (MEASURED):




LED CXM-3
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 40.0°
 Efficiency 91 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files





LED CXM-4
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 40.0°
 Efficiency 91 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files



LED COB L-Type (LES 11)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 27.0° / 52.0°
 Efficiency 88 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H





Light distribution files

OPTICAL RESULTS (MEASURED):





LED COB L-Type (LES 9)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 46.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files





LED COB S-Type (LES 7)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 44.0°
 Efficiency 91 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15848_HEKLA-SOCKET-G



Light distribution files



LED Fortimo SLM C TW L06A 1313 G7N
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 41.0°
 Efficiency 90 %
 Peak intensity 4.4 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 508 Typ L8





Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS



LED Fortimo SLM C TW L09A 1919 G7N
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 47.0°
 Efficiency 89 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K
 Bender Wirth: 501 Typ L8



Light distribution files

PHILIPS



LED Fortimo SLM L09 CoB
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 47.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files

SAMSUNG

LED LC003D / LC006D / LC009D / LC013D
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 48.0°
 Efficiency 89 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C





Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG



LED LC016D / LC019D / LC026D / LC033D
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 31.0° / 62.0°
 Efficiency 87 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

SAMSUNG



LED LC030C/040C G2
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 26.0° / 52.0°
 Efficiency 88 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files



LED MJT COB LES 14.5
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 30.0° / 60.0°
 Efficiency 87 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I




Light distribution files

OPTICAL RESULTS (MEASURED):





LED MJT COB LES 6
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 24.0° / 42.0°
Efficiency 91 %
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files





LED MJT COB LES 9.8
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 25.0° / 48.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C



Light distribution files



LED SLE G7 LES09
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 25.0° / 47.0°
Efficiency 90 %
LEDs/each optic 1
Light colour/type White
Required components:
F17435_HEKLA-G2-C





Light distribution files

OPTICAL RESULTS (MEASURED):

TRIDONIC



LED SLE G7 LES13
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 28.0° / 55.0°
 Efficiency 87 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

TRIDONIC

LED SLE G7 LES15
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 30.0° / 60.0°
 Efficiency 87 %
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files


OPTICAL RESULTS (SIMULATED):



LED V10 Gen 8-9
Ordering code CP19133_AMY-50-M-B2
FWHM / FWTM 24.0° / 47.0°
Efficiency 90 %
Peak intensity 3.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:


BJB: 47.360.1020

Light distribution files




LED V3 HD Gen 8
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 26.0° / 40.0°
Efficiency 94 %
Peak intensity 4.8 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F15253_HEKLA-SOCKET-A

Light distribution files



LED V3 HD Gen 8 FC
Ordering code CP19124_AMY-50-M-C2
FWHM / FWTM 26.0° / 40.0°
Efficiency 94 %
Peak intensity 4.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:
F15255_HEKLA-SOCKET-C


Light distribution files



OPTICAL RESULTS (SIMULATED):




LED V4 HD Gen 7
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 26.1° / 42.2°
 Efficiency 92 %
 Peak intensity 4.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files




LED V4 HD Gen 8
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 26.0° / 40.0°
 Efficiency 94 %
 Peak intensity 4.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files



LED V6 Gen 8-9
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 42.0°
 Efficiency 93 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED V6 HD Gen 8
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 42.0°
 Efficiency 93 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files




LED V8 Gen7
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 46.0°
 Efficiency 90 %
 Peak intensity 4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15253_HEKLA-SOCKET-A



Light distribution files



LED V9 HD Gen 8
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 45.0°
 Efficiency 92 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED VERO13
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 29.0° / 56.0°
 Efficiency 91 %
 Peak intensity 2.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K



Light distribution files



LED Vesta DTW 6mm
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 43.0°
 Efficiency 93 %
 Peak intensity 4.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652b Hekla

Light distribution files



LED Vesta DTW 9mm (4W/6W/12W)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 44.0°
 Efficiency 91 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 652b Hekla

Light distribution files

OPTICAL RESULTS (SIMULATED):



LED Vesta DTW 9mm (4W/6W/12W)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 26.0° / 47.0°
 Efficiency 85 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F18158_HEKLA-RZ-LENS




Light distribution files

Bender Wirth: 652b Hekla




LED Vesta SE 13mm TW
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 28.0° / 54.0°
 Efficiency 83 %
 Peak intensity 2.6 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K



Light distribution files



LED Vesta TW 9mm (12W) CSP
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.1° / 46.3°
 Efficiency 82 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU02Q Type-F
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 28.0 + 27.0° / 52.0°
 Efficiency 91 %
 Peak intensity 3.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU02x (LES10)
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 24.0° / 48.0°
 Efficiency 90 %
 Peak intensity 3.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

BJB: 47.360.1020

CITIZEN

LED CLU02x (LES10)
 Ordering code C17687_AMY-50-M
 FWHM / FWTM 24.0° / 47.0°
 Efficiency 91 %
 Peak intensity 3.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C




Light distribution files

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU02x (LES10)
 Ordering code CP19142_AMY-50-M-C2-WHT
 FWHM / FWTM 25.0° / 48.0°
 Efficiency 96 %
 Peak intensity 3.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN


LED CLU700/701/702/703
 Ordering code C17687_AMY-50-M
 FWHM / FWTM 25.1° / 42.2°
 Efficiency 93 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17435_HEKLA-G2-C



Light distribution files

CITIZEN

LED CLU700/701/702/703
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 25.1° / 42.2°
 Efficiency 92 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

BJB: 47.360.1020

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU700/701/702/703
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 26.0° / 42.0°
 Efficiency 91 %
 Peak intensity 4.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C



Light distribution files

CITIZEN

LED CLU710/711
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 24.0° / 46.0°
 Efficiency 91 %
 Peak intensity 4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

BJB: 47.360.1010

CITIZEN

LED CLU712/713
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 46.0°
 Efficiency 90 %
 Peak intensity 4.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I




Light distribution files

OPTICAL RESULTS (SIMULATED):

CITIZEN


LED CLU713 Type-F
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 26.0° / 48.0 + 49.0°
 Efficiency 92 %
 Peak intensity 3.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files

CITIZEN


LED CLU723 Type-F
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 28.0° / 56.0°
 Efficiency 91 %
 Peak intensity 2.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files



LED CMA1306
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 43.0°
 Efficiency 91 %
 Peak intensity 4.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17439_HEKLA-G2-J




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED CMU10xx
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 24.0° / 48.0°
 Efficiency 90 %
 Peak intensity 3.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1020

Light distribution files




LED CMU15xx
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 30.0° / 60.0°
 Efficiency 87 %
 Peak intensity 2.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17438_HEKLA-G2-I



Light distribution files



LED LUXEON CX Plus CoB L08 (Gen2)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 30.0° / 59.0°
 Efficiency 89 %
 Peak intensity 2.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 637a Hekla

Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON CoB 1202/1203
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 46.0°
 Efficiency 92 %
 Peak intensity 4.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H



Light distribution files




LED LUXEON CoB 1202/1203
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.1° / 46.3°
 Efficiency 89 %
 Peak intensity 3.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H



Light distribution files



LED LUXEON CoB 1202/1203
 Ordering code C17687_AMY-50-M
 FWHM / FWTM 24.1° / 46.3°
 Efficiency 91 %
 Peak intensity 4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F17437_HEKLA-G2-H



Light distribution files


OPTICAL RESULTS (SIMULATED):



LED LUXEON CoB 1204/1205
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 27.0° / 54.0°
 Efficiency 90 %
 Peak intensity 3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


Bender Wirth: 632a Hekla XL

Light distribution files



LED LUXEON CoB 1205HD
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 26.0° / 50.0°
 Efficiency 91 %
 Peak intensity 3.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H


Light distribution files



LED LUXEON CoB 1208
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 31.0° / 58.0°
 Efficiency 89 %
 Peak intensity 2.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Bender Wirth: 632a Hekla XL


Light distribution files



OPTICAL RESULTS (SIMULATED):



LED LUXEON CX Plus CoB - HD S01H4
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 25.0° / 40.0°
 Efficiency 93 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634c Bayonet35L

Light distribution files



LED LUXEON CX Plus CoB - HD S02H6
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 25.0° / 43.0°
 Efficiency 93 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634c Bayonet35L

Light distribution files



LED LUXEON CX Plus CoB - HD S04H9
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 26.0° / 47.0°
 Efficiency 92 %
 Peak intensity 3.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Bender Wirth: 634a Bayonet35L

Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON CX Plus CoB L04 / L05 (Gen2)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 27.0° / 52.0°
 Efficiency 90 %
 Peak intensity 3.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15254_HEKLA-SOCKET-B



Light distribution files




LED LUXEON CX Plus CoB M02 / M03 (Gen2)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 46.0°
 Efficiency 91 %
 Peak intensity 4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15256_HEKLA-SOCKET-D



Light distribution files



LED LUXEON CX Plus CoB S01 (Gen2)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 42.0°
 Efficiency 93 %
 Peak intensity 4.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15956_HEKLA-SOCKET-J




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED CHM-9 XH (19x19)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 44.0°
 Efficiency 92 %
 Peak intensity 4.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I



Light distribution files



LED CTM-6 (Tunable White) Gen2
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 42.0°
 Efficiency 92 %
 Peak intensity 4.5 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 495 Typ L8



LED CTM-9 (Tunable White) Gen2
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 26.0° / 46.0°
 Efficiency 91 %
 Peak intensity 3.9 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K



Light distribution files


Bender Wirth: 495 Typ L8

OPTICAL RESULTS (SIMULATED):



LED CxM-6 (13.5x13.5)
 Ordering code CP19163_AMY-35-W-B2
 FWHM / FWTM 24.0° / 42.0°
 Efficiency 92 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


BJB: 47.360.1020



Light distribution files




LED CxM-9 (13.5x13.5)
 Ordering code CP19151_AMY-50-M-B2-WHT
 FWHM / FWTM 25.0° / 48.0°
 Efficiency 90 %
 Peak intensity 3.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 C18968_SOCKET-B-35-C



Light distribution files



LED COB J-Type
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 31.0° / 59.0°
 Efficiency 89 %
 Peak intensity 2.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 663a Hekla XL

OPTICAL RESULTS (SIMULATED):




LED COB L-Type (LES 9)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 46.0°
 Efficiency 92 %
 Peak intensity 4.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15858_HEKLA-SOCKET-H



Light distribution files



LED COB S-Type (LES 6)
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 24.0° / 42.0°
 Efficiency 93 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Bender Wirth: 652a Bayonet35L



LED COB S-Type (LES 7)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 44.0°
 Efficiency 89 %
 Peak intensity 4.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

Bender Wirth: 652a Hekla


OPTICAL RESULTS (SIMULATED):



LED COB S-Type (LES 7)
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 24.0° / 42.0°
 Efficiency 93 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Bender Wirth: 652a Bayonet35L


Light distribution files



LED COB T-Type
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 24.0° / 42.0°
 Efficiency 93 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Bender Wirth: 652a Bayonet35L


Light distribution files



LED NJCWL024Z-V1MT: COB L-Type Tunable White
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 42.0°
 Efficiency 92 %
 Peak intensity 4.6 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K

Bender Wirth: 497 Typ L8 HV


Light distribution files



OPTICAL RESULTS (SIMULATED):



LED NJNWS012Z-V1MT: COB S-Type Tunable White
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 24.0° / 40.0°
 Efficiency 93 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 495 Typ L8 HV



LED NVCWJ024Z-V1MT: COB J-Type Tunable White
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 26.0° / 48.0°
 Efficiency 90 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:
 C16142_HEKLA-SOCKET-K




Light distribution files

Bender Wirth: 498 Typ L8 HV



LED LC003D / LC006D / LC009D / LC013D
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.1° / 48.3°
 Efficiency 87 %
 Peak intensity 3.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15255_HEKLA-SOCKET-C




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG

LED LC003D / LC006D / LC009D / LC013D
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 24.0° / 46.0°
 Efficiency 91 %
 Peak intensity 4.1 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1020

Light distribution files

SAMSUNG

LED LC010C G2
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 24.0° / 42.0°
 Efficiency 92 %
 Peak intensity 4.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1020

Light distribution files

SAMSUNG

LED LC010T (Tunable White)
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 25.0° / 44.0°
 Efficiency 92 %
 Peak intensity 4.2 cd/lm
 LEDs/each optic 1
 Light colour/type Tunable White
 Required components:




Bender Wirth: 501 Typ L8

Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG

LED LC020C G2
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 25.0° / 46.0°
 Efficiency 90 %
 Peak intensity 4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1010

Light distribution files

SAMSUNG

LED LC030C/040C G2
 Ordering code CP19133_AMY-50-M-B2
 FWHM / FWTM 28.0° / 52.0°
 Efficiency 89 %
 Peak intensity 3.2 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




BJB: 47.360.1010

Light distribution files



LED MJT COB LES 14.5
 Ordering code CP19124_AMY-50-M-C2
 FWHM / FWTM 30.0° / 59.0°
 Efficiency 88 %
 Peak intensity 2.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:
 F15859_HEKLA-SOCKET-I




Light distribution files

OPTICAL RESULTS (SIMULATED):

TRIDONIC

LED	SLE SNC8 LES06
Ordering code	CP19124_AMY-50-M-C2
FWHM / FWTM	24.0° / 42.0°
Efficiency	93 %
Peak intensity	4.7 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	
	F17435_HEKLA-G2-C



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)