

KWD RANGE

KWD106 Chelsea Safety Boot – S1P/S1



KING'S

by Honeywell

The Logical Choice



Description: Leather Elastic-sided Safety Boot

Size: UK 3-13 | US 4-14 | EU 36-48

Application: Mining, Manufacturing, General Industries, Utilities, Transportation, Logistics

Standard: SR (EN ISO 20345:2022); S1P/S1



SKU	Steel Midsole	Color	Outsole	Category
KWD106	Yes	Black	Dual Density PU	S1P
KWD106X	No	Black	Dual Density PU	S1

Features:

- Tough 2.0 - 2.2 mm thick full-grain leather upper with good breathability.
- Elastic-sided boot with back pull-up strap for easy donning and doffing.
- Padded ankle collar offers enhanced ankle comfort, support, and chafing prevention.
- Stability Torsion Zone offers optimal support for a wide range of foot arch profiles, helping to prevent feet pronation and supination.
- Exceptional shock absorption for elevated comfort and reduced foot fatigue.
- Outsole design engineered to complement the natural biomechanics of the walking gait.
- Wider outsole surface area provides increased contact with ground to enhance stability.
- Enhanced outsole thickness to deliver exceptional cushioning and comfort with every step.
- Strong leather upper and sole bond to withstand demanding work environments.
- Tread with deeper grip patterns and enhanced grip variations offers superior traction and stability.
- King's signature wide profile steel toecap for greater comfort.
- King's Comfort Footbed features ultra-breathable perforated channels for quick drying and all-day feet freshness.
- Highly breathable 3-D lining minimises skin abrasion, keeps feet insulated and effectively wicks away moisture.
- Lightweight, shock absorbing dual density polyurethane (PU) sole for added comfort.
- Wear-off indicators provide an early warning on sole wear and potential loss of grip.
- Excellent slip resistant sole delivers durable traction; SR (EN ISO 20345:2022); Anti-static.
- Sole resistant to mineral and organic oils.

SOLE FEATURES



Puncture Resistant



Anti-Static



Slip Resistant



Mineral Oils Resistant



Organic Oils & Fats Resistant

FOOTWEAR FEATURES



2.0 - 2.2mm
Full Grain
Leather



Wear-off Indicator



Toe Bumper



Steel Safety Toecap

COMFORT FEATURES



Wide Profile Toecap



Breathable Lining



Comfort Footbed



Impact Absorption



Lightweight



LEARN MORE
automation.honeywell.com

KWD106 | v11/24
© 2024 Honeywell International Inc.