


LR209-2RS

Galet de roulement

Yoke type track rollers LR2...-2RS/2RSR, single row self-retaining ball bearings with particularly thick-walled outer ring, ball and cage assembly and an inner ring, axial guidance of outer ring is provided by the balls, lip seal on both sides, with axial sealing action/with radial sealing action

Information technique



Votre alternative produit actuelle

joint	2RS	
profile bague extérieure	R500	Diamètre extérieur sphérique (Standard)
dispositif de lubrification	Without	Without

dimensions principale & données de performance

D	90 mm	Diamètre extérieur
d	45 mm	Alésage
C	19 mm	Hauteur
C _{r w}	23.700 N	Charge dyn. de base, radiale
C _{0r w}	14.100 N	Charge stat. de base, radiale
C _{ur w}	750 N	Limite à la fatigue, radiale
n _{D G}	3.600 1/min	Vitesse pour une lubrification à la graisse
≈m	0,28 kg	Poids

Dimensions

d ₂	53,2 mm	Diamètre rondèle de butée
r _{min}	1,1 mm	Dimension minimum de chanfrein
R	500 mm	Rayon bague extérieure profile externe



Caractéristiques



Effort radial



Effort axial uni directionnel



Effort axial dans les 2 directions



Lubrification à vie, sans entretien



Lubrification à la graisse



Etanche des 2 côtés