

M18 BSX-402C

M18™ SAWZALL™

- High performance 4-pole motor delivers maximum power whilst maximising the power to weight ratio
- REDLINK™ overload protection electronics in tool and battery pack deliver best in class system durability
- Patented FIXTEC™ clamp for fast and easy keyless blade change
- Counter balance mechanism to reduce vibrations 15.2 m/s² in wooden beams
- 28.6 mm stroke length & 3000 strokes per minute for extremely fast cutting
- Fuel gauge displays remaining charge
- REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



No load stroke rate (spm)	0 - 3,000
Stroke length (mm)	28.6
Weight with battery pack (EPTA) (kg)	4.0 (M18 B4)
Kit included	2 x M18 B4 Battery packs, M12-18 C Charger, Kitbox
Article Number	4933447290