



SurfacePro Surface Cleaner CA 30 C eco!perform

Highly concentrated, fast-drying and streak-free surface cleaner for manual maintenance cleaning. With EU Ecolabel certification.

pH value 11
in concentrate



Properties

- Universal surface cleaning concentrate
- Effectively removes food spills, grease stains, nicotine deposits, coffee stains, shoe polish, footprints, etc.
- Very good cleaning power on all water-resistant and alcohol-resistant hard and flexible surfaces
- Streak-free even on high-gloss surfaces
- Also suitable for floor cleaning
- Pleasant, fresh citrus scent
- Carries the European Ecolabel (EU Ecolabel)

Usage options

- Manual

Application areas

Building cleaning	Floor and surface cleaning
Hotels, gastronomy, catering	Floor and surface cleaning
Municipal	Floor and surface cleaning

Technical data

Container sizes	Packaging unit	Part number
1 l	12 Piece(s)	6.295-681.0
5 l	2 Piece(s)	6.295-682.0
200 l	1 Piece(s)	6.296-164.0

Application

Manual - using preconditioned mops

- Place required number of mops (10-15 mops) in the bucket.
- Pour cleaning solution over mops, 10-15 ml/mop.
- Close bucket, turn and allow to stand for 12 hours.
- Each cover cleans 20-25 m² depending on the degree of soiling.

Manual - using a mop

- Pour water into a bucket, add the required amount of cleaning agent.
- Clean surface with cloth soaked in cleaning solution.

Instructions for use

- Wear protective clothing when using the product.

Warnings and safety recommendations according to EC Directives

- EUH 210 Safety data sheet available on request.

Further information

- Material Safety Data Sheet (MSDS)
- Quick Start

Dosage and yield

Contents	Cleaning method	Dosage	Soiling	Yield
1000 ml	Maintenance cleaning	0.2 – 1 %	mild	5000 m ²