

BW 4300E

BW C43 Tool Trolley with assortment of 251 universal tools

12" 14"

Trolley with 3 stackable modules with 212 tools included for universal use.

Main features:

- Sheet metal and plastic construction
- 3 separable modules
- 1 upper basket, height 222 mm
- 1 middle module, height 168 mm with 2 drawers, height 60 mm
- 1 lower module, height 332 mm with swing door height 280 mm with wheels
- Wheels ø 128 mm
- Telescopic handle adjustable to 4 positions
- Module release system with access to all different tool compartments
- Upper basket with removable internal storage tray and 2 tool holders integrated in the lid



	Art.
043006301	BW 4300E

- n. 14 **BW 42:** Combination wrenches □
7-8-9-10-11-12-13-14-15-16-17-18-19-22 mm
- n. 9 **BW 96BPC/SC9:** Set of 9 ball head offset hexagon key wrenches □
1,5-2-2,5-3-4-5-6-8-10 mm
- n. 1 **BW 111:** Adjustable wrenches 200 mm
- n. 1 **BW 1048:** Slip joint pliers, boxed joints 250 mm
- n. 1 **BW 1052:** Adjustable self-locking pliers, concave jaws 240 mm
- n. 1 **BW 1082BM:** Diagonal cutting nippers □ 160 mm
- n. 1 **BW 1098:** Construction worker's pincers 220 mm
- n. 1 **BW 1128BMX:** Electrician's scissors, stainless steel blades, with microteeth 150 mm
- n. 1 **BW 1150BM:** Heavy-duty combination pliers □ 180 mm
- n. 1 **BW 1166BM:** Extra-long needle knurled nose pliers □ 160 mm
- n. 1 **BW 1253:** Mains testing screwdriver □ 3,5x100 mm
- n. 1 **BW 1370:** Engineer's hammers 300 g
- n. 1 **BW 1692/3:** Measuring tapes 3 m
- n. 1 **BW 1719BMA8/P:** Second-cut flat files, with handles 200 mm
- n. 1 **BW 1719BMA8/M:** Second-cut half-round files, with handles 200 mm
- n. 1 **BW 1719BMA8/R:** Second-cut round files, with handles 200 mm
- n. 1 **BW 1725CR:** Mini hacksaw frame 150 mm
- n. 10 **BW 1771RL:** 18-mm snap-off spare blades, 10 pieces, for utility knives BW 1771 and BW 1771BM 10x
- n. 1 **BW 1833S:** High-brightness LED torch, made of sturdy anodized aluminium, up to 200 lumens 105 mm Pile 1XAA (non include)
- n. 1 **BW 1390:** Soft face hammer, plastic faces Ø 35 mm
- n. 25 **BW 923E/C25:** Set of 20 hexagon socket spanners and 5 accessories, in plastic case
- n. 42 **BW 903E/C42:** Set of 13 hexagon socket spanners, 18 bits for screwdrivers 4 bent hexagon socket spanners and 7 accessories in plastic case
- n. 22 **BW 1256/C21-1:** Micro screwdriver with 21 interchangeable inserts 4 mm and handle
- n. 1 **BW 1696:** Aluminium spirit levels 300 mm
- n. 5 **1201E:** □ 2,5x50-3x75-4x100-5,5x150-6,5x150 mm
- n. 1 **1201EN:** □ 4x30 mm
- n. 3 **1202E:** □ PH0x60-PH1x80-PH2x100 mm
- n. 1 **1202EN:** □ PH1x30 mm
- n. 1 **1771:** 18 mm
- n. 100 **861/C100:**

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

