



BAG 29 PIPEFITTER TOOLS

CP-29TY

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:50:52





DESCRIPTION

BAG 29 PIPEFITTER TOOLS

3 GOOD REASONS TO CHOOSE THIS COMPOSITION

Universal clamping on the job site: The combination of open-end wrenches, adjustable spanners, and Stillson wrenches provides a secure grip on all sizes of nuts and pipes, even in hard-to-reach areas.

Precise marking and control: The compass, scribe, ruler, magnetic level, and protractor ensure reliable marks and accurate alignments before assembly.

Controlled preparation and finishing: The hacksaw, chisel, wire brush, and files allow you to cut, deburr, clean, and adjust for a clean and durable assembly.

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:50:52



SPECIFIC DATA

Designation	BAG 26 PIPEFITTER TOOLS
Sales reference	CP-29TY
Weight (kg)	12.9
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

Toolset



x 1

Textile tool case 30l
BAG-2N



x 2

Satin-finish adjustable wrenches
54-C...
Ref : 54-C10 - 54-C15



x 6

Open end wrenches in mm
10-...N
Ref : 10x11 - 12x13 - 17x19 - 22x24 - 24x27 - 30x32



x 1

Wing nut type metal saw
794



x 1

Shatterproof vial levels with magnetic bottom
166-...MN
Ref : 166-40MN



x 1

Short tape measures with two-material casings
UB-...N
Ref : UB-216N

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:50:52



	x 1	Punch 10 mm 8N-...A Ref : 8N-10A
	x 1	Stillson type pipework wrenches 632-... Ref : 632-18
	x 1	Spring type compass 782-A-... Ref : 782-A-20
	x 1	Riveting hammers 310-...N Ref : 310-42N
	x 1	Mechanic's wooden round blade slotted head screwdriver TW-...MH... Ref : TW-8MH150
	x 1	Polished varnished universal pliers 204-...P Ref : 204-16P
	x 1	Half-round files LDR-... Ref : LDR-30-M
	x 1	Flat hand file LPM-... Ref : LPM-20-BE
	x 1	Round files LR-... Ref : LR-15-M
	x 2	Wooden file handles LM-... Ref : LM-1
	x 1	High capacity bevel protractor 710-R-6
	x 1	Flexible rules 781-... Ref : 781-10
	x 1	Constant section chisels 3-...-A Ref : 3-250-A
	x 1	Constant section cape chisels 4-...-A Ref : 4-200-A

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:50:52





x 1

Plastic body scribe
665-11

PROFESSIONS AND SETS

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,¸

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:50:52

