


13A Socket Outlet with Two USB Charging Ports



Description

Metalclad offers a tough and impact resistant range of accessories with a durable finish and protective coating.

13A Socket with high current USB charging ports, for simultaneous charging of smart phones, tablets and other portable devices.

Each product is supplied with a surface mount metalclad back box and in its own polybag, protecting it up to the point of installation.

Features

- Durable and tough finish with protective coating
- Supplied complete with surface mounting box with knockouts
- Captive and backed out terminals
- Terminals have clearly embossed markings
- Only one size 4mm screwdriver needed
- Terminals have large lead-ins
- Recessed earth bar
- 2 earth terminals on 2 gang sockets
- 25-year guarantee

Technical Specification

Voltage rating	250Vac
Current rating	13A per outlet
Contact gap	3mm
USB ports output	"Phone" 5V 1,000mA "Tablet" 5V 2,400mA
Standby current	1.2mA

Switches control 13A sockets, not USB charging ports

No user serviceable parts

Standards

- BS 1363 Part 2
- BS EN 60950-1

Range

2 Gang Switched - 2 USB charging ports VM1289

Back Boxes - Knockouts

All knockouts are 20mm diameter

	Sides	Back
2g	8	1

Terminal Capacity

	2.5mm ²	4mm ²	6mm ²	10mm ²
L & N	4	3	2	1