

2504 : Mandrel / Flanging Tool

References



Sku	Description	Type	Pipe O.D. mm	kg
250441	Flanging tool	90°	6 à 14	0,090
250442	Flanging tool	90°	10 à 22	0,270
250443	Flanging tool	90°	6 to 40	0,525
250447	Flanging tool	60°	10 à 22	0,300
250422	Mandrel	Single	10	0,075
250423	Mandrel	Single	12	0,080
250435	Mandrel	Single	16	0,250
250421	Mandrel	2 sizes	8 and 14	0,085
250431	Mandrel	2 sizes	10 and 18	0,265
250432	Mandrel	2 sizes	12 and 20	0,275
250433	Mandrel	2 sizes	14 and 22	0,285
250434	Mandrel	2 sizes	15 and 22	0,290

