

BAY TROLLEYS



**600 - 1200
KG**

For transporting large panels thanks to their large bearing surface.

CHASSIS :

- Made of heavy-duty square tubing to give the whole trolley great stability and prevent it from tipping over.
- Dispensing tubes surrounded by PVC protection to protect loads from the risk of scratching.
- Side panel

RIDE QUALITY :

- 600 kg models: 4 non-marking wheels
2 fixed wheels + 2 swivel wheels with brakes, Ø 200 mm, nylon, with TPE solid rubber tyres, ball bearing
- 1200 kg models: high stability with 6 wheels
2 fixed wheels in the centre + 4 swivel wheels on the outside, 2 of which have brakes
Ball-bearing aluminium bodies allow 360° rotation on site.

SERVICE :

- Trolleys delivered READY TO USE.



800 007 297

800 006 529



Reference	CU kg	Usable dimensions (HxW) mm	Overall dimensions (WxDxH) mm	Bandage	Wheel Ø mm	Weight kg
800 007 297	600	1430 x 450	1800 x 800 x 1780	VSES	4 x 200	64
800 006 563	1200			Rubber	6 x 200	79
800 007 296	600	2 x (1430 x 250)		VSES	4 x 200	80
800 006 529	1200			Rubber	6 x 200	100



PRODUCT ZOOM



800 007 296



800 006 563