

Category 6A Extension lead



Category 6A Extension lead, 3m (SGPXZ3Bk)

TUK's Category 6A low smoke zero halogen extension leads are designed manufactured and tested in accordance with the ISO and TIA standards for Category 6A. The use of an FTP cable effectively eliminates Alien Crosstalk from adjacent leads as well as protecting the lead from emissions from any other external sources. High gold plating on contacts ensures consistent high-quality mating.

Features:

- Quick and easy extension of Category 5, 6 or 6A sockets without need for engineers
- Compliant with IEC60512-99-001 – suitable for use with IEEE 802.3at (PoE+) applications
- Terminated with high gold plated RJ45 shielded plug and socket
- Fitted with flush anti-snag strain relief boots making our leads suitable for use in high density switches
- Each lead individually tested for compliance

Specifications:

- Available as: 3m, 10m, 20m/ SGPXZ3Bk, SGPXZ10Bk, SGPXZ20Bk,
- Net weight (including primary packaging): 3m: 128g, 10m: 340g, 20m: 646g
- Dimensions: (when packed) 3m: 160x200x35mm, 10m: 190x190x50mm 20m: 190x190x50mm
- Colour: Black

Materials:

Plug

- Contacts: 50µ"/1.27µm gold plated

Cable:

- Low Smoke Zero Halogen sheath, 4 twisted pairs of 26AWG stranded copper wires individually mylar overfoiled

Socket

- ABS housing over die cast nickel-plated zinc body, contacts: 50µ"/1.27µm gold plating over nickel, over phosphor bronze - suitable for at least 500 insertions

Packaging: Supplied in individual poly bags

Commodity code: 85177090

EAN: SGPXZ3Bk: 5055386510693
SGPXZ10Bk: 5055386510709
SGPXZ20Bk: 5055386510716

Country of Origin: China

Other lengths available to order.

See also related product – Portsaver (SGTS): <https://www.tuk.co.uk/product/category-6a-portsaver>

ROHS Compliant

Code: SGPXZ*BK

