

TROLLEYS WITH FOLDING BACKRESTS



**200 to 500
KG**

Professional trucks for intensive use.



PLATFORM :

- Made of sheet metal, covered with a glued and hot-pressed non-slip rubber mat.
- Deep-drawn tray with internal reinforcements for durability and excellent strength.
- Anti-oxidation screws and bolts.

SHIKE GUARD :

- Very thick, resistant and non-staining.

HANDLEBAR :

- Double-coated for long-lasting durability.

RIDE QUALITY :

- Quiet, non-marking, heavy-duty wheels with nylon structure and rubber tyres.
- Double sealed ball bearing.
- Very low start-up effort.
- 2 fixed wheels + 2 swivel wheels.

SAFETY :

- Anti-pinch system.

SERVICE :

- Trolleys delivered READY TO USE.



Reference	CU kg	Thrust height	Plate thicknes s	Tray dimensions	Height from platform to floor	Thrust resistance	Wheel Ø mm	Brake	Weig ht kg
805 007 164	200	910	30	740 x 480	134	2,6	100	Option	12
805 006 996	300	990	45	920 x 610	210	3,1	130	Option	19

805 007 153	500	1 040	55	1240 x 790	290	5,7	200	Without brake	41
805 007 348								With brake	43



OPTIONS



Brake kit
Fits on fixed wheels
805 007 286 - For model 805 007 164
805 007 288 - For model 805 006 996



825 009 648 - Support net
Ideal for holding small loads. Fitted with 6 removable hooks, it can be quickly positioned around loads to provide excellent support.

OTHER MODELS AVAILABLE

