



M18 BLCS66-O

M18™ BRUSHLESS 66 MM CIRCULAR SAW FOR WOOD AND PLASTICS

M18™ brushless circular saw with a 190 mm blade giving a 66 mm depth of cut which enables the saw to cut three stacked 19 mm OSB boards

REDLINK™ overload protection electronics in tool and battery pack deliver best in class system durability

REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life

Durable metal rafter hang hook for work space management and safety

Vacuum adaptor supplied fits directly to all MILWAUKEE® dust extractors

Pressed aluminum shoe for maximum durability

Integrated LED light for workspace illumination

50° bevel capacity with a 46 mm depth of cut

Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



No load speed (rpm)	5,000
Max. cutting depth 90° (mm)	66
Max. cutting depth 45° (mm)	48
Blade diameter (mm)	190
Bore size (mm)	30
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933464588