

M18 VC2-0

M18™ WET/ DRY VACUUM

- Powerful 18 V motor with a maximum air flow of 1300 l/min / 80 bar provides excellent suction power for both wet and dry clean up applications
- HEPA filter will collect 99.97% of airborne particles down to 0.03 microns for fine dust collection
- Up to 30 minutes run time with M18™ 9.0 Ah battery pack
- Internal accessory and hose storage allows all attachments to be carried with the tool avoiding loss of equipment
- DEK 26 compatible allows the vacuum to be easily connected to a power tool
- Stackable tool box design for added portability and easier storage
- On board blower for moving debris away from the work area
- Waterproof switch prevents switch damage over the life time of the tool
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™

Capacity solids (l)	9.79
Capacity liquids (l)	7.5
Hose diameter (mm)	41
Hose length (m)	0.47
Weight with battery pack (EPTA) (kg)	5.3 (M18 B5)
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933464029