


50A DP Switches



Description

This uniquely shaped range is easy to install, with clear bold terminal markings and is supplied in individual protective polybags suitable for display.

This range includes neon versions, red switches and an option of square or tall versions.

Features

- Contemporary Designed Profile
- Concave rockers
- Only one size 4mm screwdriver needed
- Grey font engraving
- Terminals have clear bold markings
- Square or tall versions available
- Neon versions available
- Neon leads enclosed
- 2 Earth terminals
- Terminals have large lead-ins
- 25-year guarantee

Range

Red Switch	VP1300
Red Switch with neon	VP1300N
Tall red switch	VP1301
Tall red switch with neon	VP1301N

Technical Specification

Voltage rating	250Vac
Current Rating	50A per outlet
Contact gap	3mm
Front plate material	Urea formaldehyde

Urea flammability classification UL94 grade V-C

No user serviceable parts

For use as an Isolator switch, not for functional switching

Back Boxes

Minimum recommended depth

	Flush 47mm	Dry lining 46mm	Surface 46mm
1g	DB167	DB2542	VP1228
2g	DB168	DB2543	VP1229

Standards

- BS EN 60669-1

Terminal Capacity

	6mm ²	10mm ²
L & N	2	1