

# KERN OBB-A3204

Achromatic objective, 10x /0,25 W.D. (7 mm)

**KERN**

REACH classification

no prohibited substances

Pictograms

STANDARD



## Category

|                  |                                    |
|------------------|------------------------------------|
| Brand            | Optics                             |
| Product category | Optical Instrument                 |
| Product group    | Microscope objective<br>achromatic |

## Construction

|                   |             |
|-------------------|-------------|
| Dimension (W×D×H) | 30×25×25 mm |
|-------------------|-------------|

## Objective

|                            |            |
|----------------------------|------------|
| Objective magnification    | 10x        |
| Objective quality          | Achromatic |
| Numerical Aperture         | 0,25       |
| Objective working distance | 7 mm       |

## Environmental conditions

|                           |       |
|---------------------------|-------|
| Storage temperature [Min] | -5 °C |
| Storage temperature [Max] | 40 °C |

## Packing & Shipping

|                              |                |
|------------------------------|----------------|
| Delivery time                | 1 d            |
| Dimensions packaging (W×D×H) | 65×40×40 mm    |
| Shipping method              | Parcel service |
| Net weight approx.           | 0,30 kg        |
| Gross weight approx.         | 0,60 kg        |
| Shipping weight              | 0,6 kg         |
| Shipping volume weight       | 0,1 kg         |

## Product information

|                 |               |
|-----------------|---------------|
| GTIN/EAN number | 4045761237438 |
| Trade number    | 90119000      |