


KERN 366-88

KERN

Individual weight, OIML Class M3, 20 kg, Block, cast iron lacquered



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M3
Product family	366

Measuring System

Test weight - nominal value	20 kg
Test weight - volume uncertainty (cm ³)	238,048
Weight OIML class	M3
Conformity assessment possible	no
Test weight - volume (cm ³)	2816,9014
Permissible tolerance according to OIML (+/-)	10 g
OIML-compliant	✓
Test weight - Density [Min] (OIML)	1500
Test weight - Density (kg/m ³)	7100
Test weight - Density uncertainty (kg/m ³)	600

Construction

Shape weight	Block
Dimensions weight (W×D×H)	230×115×139 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-645
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	230×115×139 mm
Shipping method	Parcel service
Net weight approx.	20 kg
Gross weight approx.	20 kg
Shipping weight	20 kg
Shipping volume weight	0,7 kg

Optional cases

Case - Aluminium article number	346-080-600
---------------------------------	-------------

Product information

GTIN/EAN number	4045761012011
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

