

POEV 125/15XR-SG

Heavy duty wheel, with 'Blickle EasyRoll' elastic solid rubber tyres, with nylon wheel centre, non-marking, grey

EAN 4047526008871

ID 8870

Customs tariff number 87169090



Tyre:

- high-quality elastic solid rubber "Blickle EasyRoll" in smooth rolling quality, hardness 65 Shore A
- very good operational comfort
- very good floor preservation, low-noise operation
- low rolling resistance
- colour grey, non-marking
- vulcanised onto the wheel centre

Wheel centre:

- high-quality nylon 6, impact resistant
- colour black

Other features:

- high chemical resistance to many aggressive substances, except oils
- operating temperature: -25 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +35 °C



Technical data:

Wheel Ø (D)	☉	125 mm
Wheel width	⌈⌋	37 mm
Load capacity at 4 km/h	⚖	250 kg
Load capacity (static)	⚖	625 kg
Bearing type	☉	roller bearing
Axle bore Ø (d)		15 mm
Hub keyway (T1)	⌈⌋	45 mm
Temperature resistance min		-25 °C
Temperature resistance max		80 °C
Tread and tyre hardness		65 Shore A
Unit weight	⚖	0.3 kg
Non-marking		✓
Non-staining		✓
Antistatic	⚡	✗
ESD		✗
Electrically conductive	⚡	✗
Corrosion-resistant		✓
Heat-resistant	🔥	✗
Suitable for autoclaves		✗

Tread and tyre hardness

■ ■ ■ ■ ■ 65 Shore A

Rolling resistance

■ ■ ■ ■ ■ very good

Wear resistance

■ ■ ■ ■ ■ good

Operating noise / floor surface preservation

■ ■ ■ ■ ■ very good

