

Features

- Easy-to-handle strong shears, ideal for the cutting of copper wire, other soft material, ferrous wire and memory wire.
- Tools is equipped with a return spring designed to have a constant force, thus reducing operator effort.
- The anti-slip bi-material dolphin EVO handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator.
- Laser marking.
- MADE IN ITALY.

RS PRO Shears.

RS Stock No.: 0845448



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Shear ideal for cutting of copper wire, other soft materials, ferrous wire and memory wire. Typical applications include different tasks in microelectronics, jewellery making, laboratory, watch making and repairs, DIY and medical fields in mild aggressive chemical environments. The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.

General Specifications

Point Type	
Cutting capacity – ferrous wire	Ø 2.00 mm (12 awg)
Cutting capacity – memory wire	Ø 0.50 mm (24 awg)
Material	High Carbon Steel
Steel thickness	3 mm
Width of the head	20 mm
Length of the tool	135 mm +/- 2 mm
Net weight	83,7 g +/- 2 g
Lock	Locking lever

