

Stealth™ 7000

Incolore certifié K / ASA430-021-300



DESCRIPTION

Les lunettes Stealth™ 7000 sont dotées d'un design aux contours bien définis et d'une monture flexible pour un ajustement polyvalent, couvrant différentes tailles de visage. Les matières légères et un design simplifié s'associent pour offrir un port continu confortable, disponible dans une large gamme de teintes d'oculaires.

OPTIONS

Ambré certifié K (ASA430-020-200)

Incolore certifié anti-buée N (ASA430-151-300)

Incolore certifié K (ASA430-021-300)

Oculaire miroir rouge fumé HC (ASA430-02K-100)

Fumé certifié K (ASA430-026-400)

NORMES

EN 170 • EN 166



INFORMATIONS TECHNIQUES



RADIATION PROTECTION BREAKDOWN filtering effect
Scale Number
2C



LIGHT TRANSMISSION BREAKDOWN Lens Shade number
1,2



Manufacturer's Trademark
JSP Dagger



Low Energy Impact resists a 6 mm, 0.86g ball @ 45 m/s °
Maximum protection for glasses
F



Optical Class (1 – Class 1 – High quality for regular use. 2 – Class 2 – Medium quality for occasional use. 3 – Class 3 – Low quality for exceptional use)
1



Resistance to Surface Damage by Fine Particles (optional)
K



The letter T, immediately after the mechanical strength symbol, authorises use for high speed particles at extreme temperatures. (-5°C and +55°C) Optional
T

CARACTÉRISTIQUES



Confort

Le design enveloppant assure une bonne flexibilité de la monture et permet un bon ajustement polyvalent sur des visages à la fois plus petits et plus grands.



Teintes d'oculaires

Disponible dans une large gamme de teinte d'oculaires, adaptées à différentes tâches et de multiples environnements.



Personnalisation

Le logo de votre entreprise peut être imprimé sur les branches de la lunette Stealth™ 7000.

LOGO

☒ Côtés

GAMME

**STEALTH
7000**

TÉLÉCHARGEMENTS

[Pack d'images \(ZIP\)](#)

[doc-stealth-7000-spectacle-range.pdf \(PDF\)](#)



JSP Limited. Worsham Mill. Minster Lovell. Oxford OX29 0TA. England.

Tel: +44 (0)1993 826050 / Fax: +44 (0)1993 824411 / Email: sales@jspsafety.com / Web: www.jspsafety.com

Do Not Publish without written permission from JSP Limited. Contact copyright@jspsafety.com. Information correct in the United Kingdom at date of issue and may be subject to change. Any third-party machine and automated translations processed by users may have inaccuracies and should not be relied upon.

Page 2 of 2 / Issued 26 Mar 2025 / Copyright 2018 - 2025. JSP Limited. All Rights Reserved.

